

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287631

Luminaire Tested: P3AS17R559030D2WDE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287631
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559030D2WDE010 E3DLP1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,
E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1048.0 lumens
Efficiency: N/A
Efficacy: 38.4 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287631

CATALOG NUMBER: P3AS17R559030D2WDE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1287631

CATALOG NUMBER: P3AS17R559030D2WDE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	285087
5°	277943
10°	258401
15°	230103
20°	195527
25°	157799
30°	120297
35°	85554
40°	56449
45°	33492
50°	19650
55°	12119
60°	10745
65°	9703
70°	8335
75°	7286
80°	7324
85°	7296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33492 cd/sqm

TEST NUMBER: P1287631

CATALOG NUMBER: P3AS17R559030D2WDE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.2	11.2
10°-20°	281.0	26.8
20°-30°	297.6	28.4
30°-40°	201.1	19.2
40°-50°	88.2	8.4
50°-60°	31.6	3.0
60°-70°	18.5	1.8
70°-80°	9.7	0.9
80°-90°	3.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	695.9	66.4
0°-40°	897.0	85.6
0°-60°	1016.7	97.0
0°-90°	1048.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1048.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1300	
5°	1263	117
15°	1014	281
25°	652	298
35°	320	201
45°	108	88
55°	32	32
65°	19	19
75°	9	10
85°	3	3
90°	0	

TEST NUMBER: P1287631

CATALOG NUMBER: P3AS17R559030D2WDE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1300.1
2.5°	1290.0
5°	1262.7
7.5°	1218.0
10°	1160.5
12.5°	1091.3
15°	1013.6
17.5°	927.2
20°	837.9
22.5°	744.4
25°	652.2
27.5°	561.5
30°	475.1
32.5°	393.1
35°	319.6
37.5°	253.4
40°	197.2
42.5°	148.3
45°	108.0
47.5°	79.2
50°	57.6
52.5°	40.3
55°	31.7
57.5°	28.8
60°	24.5
62.5°	21.6
65°	18.7
67.5°	15.8
70°	13.0
72.5°	11.5
75°	8.6
77.5°	7.2
80°	5.8
82.5°	4.3
85°	2.9
87.5°	1.4
90°	0.0

(END OF REPORT)