

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287637

Luminaire Tested: P3AS17R609030D2WDE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287637
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609030D2WDE010 E3CD1MB
Description: 3in Adjustable Dim to Warm LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3CD1MI
TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1862.0 lumens
Efficiency: N/A
Efficacy: 68.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287637

CATALOG NUMBER: P3AS17R609030D2WDE010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1287637

CATALOG NUMBER: P3AS17R609030D2WDE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	100	98		97	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	96	91	88		101	95	90	87		92	89	85		90	87	84		88	85	83
4	98	90	85	81		96	89	84	80		87	83	79		85	81	78		83	80	77
5	93	84	79	74		91	84	78	74		82	77	73		80	76	73		79	75	72
6	88	79	73	69		87	79	73	69		77	72	68		76	71	68		74	70	68
7	84	75	69	64		82	74	68	64		73	68	64		71	67	64		70	66	63
8	80	70	64	60		78	70	64	60		69	64	60		68	63	60		67	63	59
9	76	66	61	57		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		62	56	53		61	56	53		60	56	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	444635
5°	427007
10°	439627
15°	445292
20°	393178
25°	331374
30°	268750
35°	175017
40°	80379
45°	30825
50°	10302
55°	2753
60°	2544
65°	2231
70°	1859
75°	2457
80°	1768
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30825 cd/sqm

TEST NUMBER: P1287637

CATALOG NUMBER: P3AS17R609030D2WDE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.7	10.0
10°-20°	537.1	28.8
20°-30°	626.5	33.6
30°-40°	404.3	21.7
40°-50°	90.6	4.9
50°-60°	9.1	0.5
60°-70°	4.3	0.2
70°-80°	2.5	0.1
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1350.4	72.5
0°-40°	1754.6	94.2
0°-60°	1854.3	99.6
0°-90°	1862.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1862.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2028	
5°	1940	187
15°	1962	537
25°	1370	627
35°	654	404
45°	99	91
55°	7	9
65°	4	4
75°	3	2
85°	1	1
90°	0	

TEST NUMBER: P1287637

CATALOG NUMBER: P3AS17R609030D2WDE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2027.7
2.5°	1994.6
5°	1939.9
7.5°	1937.0
10°	1974.4
12.5°	1998.9
15°	1961.5
17.5°	1849.1
20°	1684.9
22.5°	1513.6
25°	1369.6
27.5°	1228.4
30°	1061.4
32.5°	865.5
35°	653.8
37.5°	446.4
40°	280.8
42.5°	168.5
45°	99.4
47.5°	57.6
50°	30.2
52.5°	10.1
55°	7.2
57.5°	5.8
60°	5.8
62.5°	4.3
65°	4.3
67.5°	4.3
70°	2.9
72.5°	2.9
75°	2.9
77.5°	1.4
80°	1.4
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)