

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287641

Luminaire Tested: P3AS17R609030D2WDE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287641
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609030D2WDE010 E3D1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1726.0 lumens
Efficiency: N/A
Efficacy: 63.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287641
CATALOG NUMBER: P3AS17R609030D2WDE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1287641
 CATALOG NUMBER: P3AS17R609030D2WDE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82				82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77				77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67				67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63				63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59				59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56				56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53				53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	452244
5°	426919
10°	415824
15°	406313
20°	377800
25°	337737
30°	257964
35°	148944
40°	57794
45°	24096
50°	5288
55°	803
60°	614
65°	363
70°	449
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24096 cd/sqm



TEST NUMBER: P1287641
 CATALOG NUMBER: P3AS17R609030D2WDE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.1	10.6
10°-20°	498.6	28.9
20°-30°	624.4	36.2
30°-40°	349.1	20.2
40°-50°	66.4	3.8
50°-60°	3.4	0.2
60°-70°	0.8	0.0
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1306.1	75.7
0°-40°	1655.2	95.9
0°-60°	1724.9	99.9
0°-90°	1726.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1726.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2062	
5°	1940	183
15°	1790	499
25°	1396	624
35°	556	349
45°	78	66
55°	2	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1287641
CATALOG NUMBER: P3AS17R609030D2WDE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2062.4
1°	2053.9
2°	2027.1
3°	1995.3
4°	1965.6
5°	1939.5
6°	1919.7
7°	1902.8
8°	1890.1
9°	1878.1
10°	1867.5
11°	1856.9
12°	1844.9
13°	1830.1
14°	1812.4
15°	1789.8
16°	1762.3
17°	1731.2
18°	1695.9
19°	1655.7
20°	1619.0
21°	1579.4
22°	1538.5
23°	1495.4
24°	1448.1
25°	1395.9
26°	1334.4
27°	1265.9
28°	1189.0
29°	1107.1
30°	1018.8
31°	929.9
32°	838.1
32.5°	787.9
33°	742.8
34°	648.9
35°	556.4
36°	473.1
37°	384.8
37.5°	344.6
38°	305.0
39°	245.7
40°	201.9
42.5°	122.9
45°	77.7



TEST NUMBER: P1287641
CATALOG NUMBER: P3AS17R609030D2WDE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	43.1
50°	15.5
52.5°	3.5
55°	2.1
57.5°	1.4
60°	1.4
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)