

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287680

Luminaire Tested: P3AS17R659030D2WDE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287680
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659030D2WDE010 E3DLD1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 556.0 lumens
Efficiency: N/A
Efficacy: 20.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287680
CATALOG NUMBER: P3AS17R659030D2WDE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1287680
 CATALOG NUMBER: P3AS17R659030D2WDE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98939
5°	97600
10°	94342
15°	88968
20°	82070
25°	74496
30°	65985
35°	56135
40°	44684
45°	31538
50°	18319
55°	9978
60°	9298
65°	8406
70°	7694
75°	7202
80°	6188
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 31538 cd/sqm



TEST NUMBER: P1287680

CATALOG NUMBER: P3AS17R659030D2WDE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.7	7.5
10°-20°	109.6	19.7
20°-30°	140.9	25.3
30°-40°	130.4	23.4
40°-50°	78.7	14.2
50°-60°	26.8	4.8
60°-70°	16.1	2.9
70°-80°	9.1	1.6
80°-90°	2.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	292.3	52.6
0°-40°	422.6	76.0
0°-60°	528.2	95.0
0°-90°	556.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	556.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	451	
5°	443	42
15°	392	110
25°	308	141
35°	210	130
45°	102	79
55°	26	27
65°	16	16
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1287680

CATALOG NUMBER: P3AS17R659030D2WDE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	451.2
2.5°	449.1
5°	443.4
7.5°	435.0
10°	423.7
12.5°	409.6
15°	391.9
17.5°	372.8
20°	351.7
22.5°	329.8
25°	307.9
27.5°	284.6
30°	260.6
32.5°	236.6
35°	209.7
37.5°	183.6
40°	156.1
42.5°	128.5
45°	101.7
47.5°	77.0
50°	53.7
52.5°	33.9
55°	26.1
57.5°	23.3
60°	21.2
62.5°	18.4
65°	16.2
67.5°	14.1
70°	12.0
72.5°	10.6
75°	8.5
77.5°	7.1
80°	4.9
82.5°	3.5
85°	2.1
87.5°	1.4
90°	0.0

(END OF REPORT)