

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289801

Luminaire Tested: P3AS05R45W2N902750DE010 E3DLP1WH\_2700K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1289801  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R45W2N902750DE010 E3DLP1WH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI ,  
E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 401.1 lumens  
Efficiency: N/A  
Efficacy: 68.0 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1289801

CATALOG NUMBER: P3AS05R45W2N902750DE010 E3DLP1WH\_2700K

### Luminous Intensity Polar Plot



TEST NUMBER: P1289801

CATALOG NUMBER: P3AS05R45W2N902750DE010 E3DLP1WH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |  |  |  |    |  |  |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|--|--|--|----|--|--|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    | 20 |  |  |  | 20 |  |  |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    |    | 0  |  |  |  | 0  |  |  |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0  |  |  |  | 0  |  |  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |  |  |  |    |  |  |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    |  |  |  |    |  |  |  | 100 |
| 1   | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96  | 94  |    |    |    |  |  |  |    |  |  |  | 94  |
| 2   | 109 | 104 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 96  | 94  | 96  | 94  | 92  | 93  | 91  | 90  | 88  |    |    |    |  |  |  |    |  |  |  | 88  |
| 3   | 104 | 98  | 93  | 89  | 102 | 96  | 92  | 88  | 94  | 90  | 87  | 91  | 88  | 86  | 89  | 86  | 84  | 83  |    |    |    |  |  |  |    |  |  |  | 83  |
| 4   | 99  | 92  | 87  | 83  | 97  | 91  | 86  | 82  | 89  | 85  | 81  | 87  | 83  | 80  | 85  | 82  | 79  | 78  |    |    |    |  |  |  |    |  |  |  | 78  |
| 5   | 94  | 87  | 81  | 77  | 93  | 86  | 81  | 77  | 84  | 80  | 76  | 82  | 79  | 76  | 81  | 78  | 75  | 74  |    |    |    |  |  |  |    |  |  |  | 74  |
| 6   | 90  | 82  | 76  | 73  | 89  | 81  | 76  | 72  | 80  | 75  | 72  | 78  | 74  | 71  | 77  | 74  | 71  | 69  |    |    |    |  |  |  |    |  |  |  | 69  |
| 7   | 86  | 78  | 72  | 68  | 85  | 77  | 72  | 68  | 76  | 71  | 68  | 75  | 71  | 67  | 74  | 70  | 67  | 66  |    |    |    |  |  |  |    |  |  |  | 66  |
| 8   | 83  | 74  | 68  | 65  | 82  | 73  | 68  | 64  | 72  | 68  | 64  | 71  | 67  | 64  | 70  | 67  | 64  | 62  |    |    |    |  |  |  |    |  |  |  | 62  |
| 9   | 79  | 70  | 65  | 61  | 78  | 70  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 61  | 67  | 63  | 61  | 59  |    |    |    |  |  |  |    |  |  |  | 59  |
| 10  | 76  | 67  | 62  | 58  | 75  | 67  | 62  | 58  | 66  | 61  | 58  | 65  | 61  | 58  | 65  | 61  | 58  | 57  |    |    |    |  |  |  |    |  |  |  | 57  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 150580 |
| 5°  | 147061 |
| 10° | 135179 |
| 15° | 114552 |
| 20° | 88861  |
| 25° | 62133  |
| 30° | 39145  |
| 35° | 23048  |
| 40° | 13024  |
| 45° | 6326   |
| 50° | 2217   |
| 55° | 1797   |
| 60° | 1710   |
| 65° | 1660   |
| 70° | 1603   |
| 75° | 1525   |
| 80° | 1389   |
| 85° | 1006   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 6326 cd/sqm

TEST NUMBER: P1289801

CATALOG NUMBER: P3AS05R45W2N902750DE010 E3DLP1WH\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 61.8   | 15.4      |
| 10°-20°   | 138.6  | 34.5      |
| 20°-30°   | 117.7  | 29.3      |
| 30°-40°   | 56.1   | 14.0      |
| 40°-50°   | 16.9   | 4.2       |
| 50°-60°   | 4.3    | 1.1       |
| 60°-70°   | 3.2    | 0.8       |
| 70°-80°   | 1.9    | 0.5       |
| 80°-90°   | 0.6    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 318.1  | 79.3      |
| 0°-40°    | 374.2  | 93.3      |
| 0°-60°    | 395.4  | 98.6      |
| 0°-90°    | 401.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 401.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 687 |      |
| 5°  | 668 | 62   |
| 15° | 505 | 139  |
| 25° | 257 | 118  |
| 35° | 86  | 56   |
| 45° | 20  | 17   |
| 55° | 5   | 4    |
| 65° | 3   | 3    |
| 75° | 2   | 2    |
| 85° | 0   | 1    |
| 90° | 0   |      |



TEST NUMBER: P1289801

CATALOG NUMBER: P3AS05R45W2N902750DE010 E3DLP1WH\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 686.7 |
| 2.5°  | 682.4 |
| 5°    | 668.1 |
| 7.5°  | 643.4 |
| 10°   | 607.1 |
| 12.5° | 559.1 |
| 15°   | 504.6 |
| 17.5° | 444.0 |
| 20°   | 380.8 |
| 22.5° | 316.7 |
| 25°   | 256.8 |
| 27.5° | 202.3 |
| 30°   | 154.6 |
| 32.5° | 116.2 |
| 35°   | 86.1  |
| 37.5° | 63.5  |
| 40°   | 45.5  |
| 42.5° | 31.6  |
| 45°   | 20.4  |
| 47.5° | 11.5  |
| 50°   | 6.5   |
| 52.5° | 5.0   |
| 55°   | 4.7   |
| 57.5° | 4.3   |
| 60°   | 3.9   |
| 62.5° | 3.6   |
| 65°   | 3.2   |
| 67.5° | 2.9   |
| 70°   | 2.5   |
| 72.5° | 2.2   |
| 75°   | 1.8   |
| 77.5° | 1.4   |
| 80°   | 1.1   |
| 82.5° | 0.7   |
| 85°   | 0.4   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)