

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287690

Luminaire Tested: P3AS17R659030D2WDE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287690
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659030D2WDE010 E3DLP1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1444.0 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287690

CATALOG NUMBER: P3AS17R659030D2WDE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1287690

CATALOG NUMBER: P3AS17R659030D2WDE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	340543
5°	336451
10°	323686
15°	303203
20°	272720
25°	231570
30°	181116
35°	129081
40°	84473
45°	52222
50°	26507
55°	9366
60°	8201
65°	8198
70°	7373
75°	7286
80°	7324
85°	7296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 52222 cd/sqm

TEST NUMBER: P1287690

CATALOG NUMBER: P3AS17R659030D2WDE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.5	9.9
10°-20°	371.7	25.7
20°-30°	434.4	30.1
30°-40°	303.6	21.0
40°-50°	133.6	9.3
50°-60°	29.8	2.1
60°-70°	15.1	1.0
70°-80°	9.1	0.6
80°-90°	3.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	949.7	65.8
0°-40°	1253.3	86.8
0°-60°	1416.6	98.1
0°-90°	1444.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1444.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1553	
5°	1528	144
15°	1336	372
25°	957	434
35°	482	304
45°	168	134
55°	24	30
65°	16	15
75°	9	9
85°	3	3
90°	0	

TEST NUMBER: P1287690

CATALOG NUMBER: P3AS17R659030D2WDE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1553.0
2.5°	1547.2
5°	1528.5
7.5°	1496.8
10°	1453.7
12.5°	1400.4
15°	1335.6
17.5°	1256.5
20°	1168.7
22.5°	1069.4
25°	957.1
27.5°	839.1
30°	715.3
32.5°	595.9
35°	482.2
37.5°	382.8
40°	295.1
42.5°	223.1
45°	168.4
47.5°	123.8
50°	77.7
52.5°	40.3
55°	24.5
57.5°	21.6
60°	18.7
62.5°	17.3
65°	15.8
67.5°	13.0
70°	11.5
72.5°	10.1
75°	8.6
77.5°	7.2
80°	5.8
82.5°	4.3
85°	2.9
87.5°	1.4
90°	0.0

(END OF REPORT)