

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287980

Luminaire Tested: P3AS05R15W2N902765DE010 E3DLD1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287980
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R15W2N902765DE010 E3DLD1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 153.0 lumens
Efficiency: N/A
Efficacy: 25.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287980

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3DLD1GPH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1287980

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3DLD1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83		
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	74	69	66	65		
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60		
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56		
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38593
5°	37552
10°	34312
15°	30057
20°	25786
25°	21534
30°	17218
35°	12930
40°	9389
45°	6140
50°	3821
55°	2600
60°	2281
65°	2127
70°	1988
75°	1779
80°	1768
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6140 cd/sqm

TEST NUMBER: P1287980

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3DLD1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.7	10.3
10°-20°	36.9	24.1
20°-30°	40.6	26.6
30°-40°	30.4	19.9
40°-50°	15.8	10.3
50°-60°	6.5	4.3
60°-70°	4.1	2.7
70°-80°	2.3	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	93.3	61.0
0°-40°	123.7	80.8
0°-60°	146.0	95.4
0°-90°	153.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	153.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	176	
5°	171	16
15°	132	37
25°	89	41
35°	48	30
45°	20	16
55°	7	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1287980

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	176.0
1°	176.2
2°	175.6
3°	174.4
4°	172.7
5°	170.6
6°	167.9
7°	164.9
8°	161.5
9°	157.8
10°	154.1
12.5°	143.4
15°	132.4
17.5°	121.3
20°	110.5
22.5°	99.4
25°	89.0
27.5°	78.5
30°	68.0
32.5°	57.8
35°	48.3
37.5°	40.1
40°	32.8
42.5°	26.0
45°	19.8
47.5°	14.9
50°	11.2
52.5°	8.3
55°	6.8
57.5°	6.0
60°	5.2
62.5°	4.7
65°	4.1
67.5°	3.5
70°	3.1
72.5°	2.5
75°	2.1
77.5°	1.7
80°	1.4
82.5°	1.0
85°	0.6
87.5°	0.2
90°	0.0

(END OF REPORT)