

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288013

Luminaire Tested: P3AS05R15W2N902765DE010 E3DLD1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R15W2N902765DE010 E3DLD1WMH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 5000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 315.1 lumens
Efficiency: N/A
Efficacy: 53.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288013

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3DLD1WMH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288013

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3DLD1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96	95	93	91
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90	87	85	83
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84	81	78	76
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78	75	72	70
5	89	80	73	68	87	79	73	68	77	72	67		75	70	67		74	69	66	65
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69	65	61	60
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65	61	57	56
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61	57	53	52
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58	53	50	49
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79445
5°	77306
10°	70629
15°	61885
20°	53088
25°	44325
30°	35474
35°	26609
40°	19293
45°	12621
50°	7880
55°	5352
60°	4736
65°	4358
70°	4103
75°	3728
80°	3536
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 12621 cd/sqm

TEST NUMBER: P1288013

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3DLD1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.4	10.3
10°-20°	75.9	24.1
20°-30°	83.7	26.6
30°-40°	62.7	19.9
40°-50°	32.5	10.3
50°-60°	13.5	4.3
60°-70°	8.4	2.7
70°-80°	4.7	1.5
80°-90°	1.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	192.0	61.0
0°-40°	254.7	80.8
0°-60°	300.6	95.4
0°-90°	315.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	315.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	362	
5°	351	32
15°	273	76
25°	183	84
35°	99	63
45°	41	32
55°	14	13
65°	8	8
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1288013

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3DLD1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	362.3
1°	362.7
2°	361.5
3°	359.1
4°	355.6
5°	351.2
6°	345.6
7°	339.6
8°	332.4
9°	324.8
10°	317.2
12.5°	295.3
15°	272.6
17.5°	249.8
20°	227.5
22.5°	204.7
25°	183.2
27.5°	161.6
30°	140.1
32.5°	118.9
35°	99.4
37.5°	82.6
40°	67.4
42.5°	53.5
45°	40.7
47.5°	30.7
50°	23.1
52.5°	17.2
55°	14.0
57.5°	12.4
60°	10.8
62.5°	9.6
65°	8.4
67.5°	7.2
70°	6.4
72.5°	5.2
75°	4.4
77.5°	3.6
80°	2.8
82.5°	2.0
85°	1.2
87.5°	0.4
90°	0.0

(END OF REPORT)