

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288048

Luminaire Tested: P3AS05R15W2N902765DE010 E3DLP1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288048
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R15W2N902765DE010 E3DLP1WMH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 247.0 lumens
Efficiency: N/A
Efficacy: 41.9 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288048

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3DLP1WMH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288048

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3DLP1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	73	78	75	72	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106505
5°	98437
10°	78600
15°	59365
20°	45201
25°	34454
30°	24687
35°	16115
40°	9876
45°	5985
50°	3957
55°	3058
60°	2631
65°	2283
70°	2052
75°	2033
80°	1515
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5985 cd/sqm

TEST NUMBER: P1288048

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3DLP1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.6	16.0
10°-20°	73.1	29.6
20°-30°	65.1	26.4
30°-40°	38.5	15.6
40°-50°	15.8	6.4
50°-60°	7.4	3.0
60°-70°	4.5	1.8
70°-80°	2.4	1.0
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	177.8	72.0
0°-40°	216.3	87.6
0°-60°	239.5	97.0
0°-90°	247.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	247.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	486	
5°	447	40
15°	262	73
25°	142	65
35°	60	39
45°	19	16
55°	8	7
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1288048

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3DLP1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	485.7
1°	484.5
2°	480.9
3°	473.7
4°	461.7
5°	447.2
6°	431.6
7°	413.1
8°	393.9
9°	374.2
10°	353.0
12.5°	304.4
15°	261.5
17.5°	224.6
20°	193.7
22.5°	166.5
25°	142.4
27.5°	119.1
30°	97.5
32.5°	77.8
35°	60.2
37.5°	46.1
40°	34.5
42.5°	25.7
45°	19.3
47.5°	14.8
50°	11.6
52.5°	9.6
55°	8.0
57.5°	6.8
60°	6.0
62.5°	5.2
65°	4.4
67.5°	4.0
70°	3.2
72.5°	2.8
75°	2.4
77.5°	1.6
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)