

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288095

Luminaire Tested: P3AS05R20W2N902750DE010 E3CD1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R20W2N902750DE010 E3CD1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3CD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 499.0 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288095

CATALOG NUMBER: P3AS05R20W2N902750DE010 E3CD1MW_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288095

CATALOG NUMBER: P3AS05R20W2N902750DE010 E3CD1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	102	102	102	102	102	102	102	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	99	98	97	97	96	95	95	94	93	93	92	91
2	112	109	107	104	110	108	105	103	104	103	101	102	100	99	99	98	97	97	96	95	95	94	93	93	92	91	91	90	89
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	95	94	93	93	92	91	91	90	89	88	87	86
4	107	102	99	96	105	101	98	96	99	97	94	97	95	93	96	94	92	92	91	90	90	89	88	87	86	85	84	83	82
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	91	90	89	89	88	87	86	85	84	83	82	81
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	89	88	87	87	86	85	84	83	82	81	80	79
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	87	86	85	85	84	83	82	81	80	79	78	77
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	85	84	83	83	82	81	80	79	78	77	76	75
9	96	90	87	85	95	90	87	85	89	86	84	88	86	84	87	85	83	83	82	81	81	80	79	78	77	76	75	74	73
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	86	84	82	82	81	80	80	79	78	77	76	75	74	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	775004
5°	672682
10°	415646
15°	144360
20°	44337
25°	15678
30°	5798
35°	2329
40°	1231
45°	496
50°	273
55°	306
60°	351
65°	208
70°	256
75°	339
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 496 cd/sqm

TEST NUMBER: P1288095

CATALOG NUMBER: P3AS05R20W2N902750DE010 E3CD1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	253.6	50.8
10°-20°	201.2	40.3
20°-30°	34.8	7.0
30°-40°	6.3	1.3
40°-50°	1.5	0.3
50°-60°	0.7	0.1
60°-70°	0.4	0.1
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	489.7	98.1
0°-40°	496.0	99.4
0°-60°	498.2	99.8
0°-90°	499.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	499.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3534	
5°	3056	254
15°	636	201
25°	65	35
35°	9	6
45°	2	1
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1288095

CATALOG NUMBER: P3AS05R20W2N902750DE010 E3CD1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3534.3
1°	3517.3
2°	3450.2
3°	3342.3
4°	3215.9
5°	3056.0
6°	2872.7
7°	2659.4
8°	2416.5
9°	2143.6
10°	1866.7
12.5°	1177.4
15°	635.9
17.5°	339.7
20°	190.0
22.5°	108.6
25°	64.8
27.5°	39.5
30°	22.9
32.5°	13.4
35°	8.7
37.5°	5.9
40°	4.3
42.5°	2.8
45°	1.6
47.5°	0.8
50°	0.8
52.5°	0.8
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)