

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290505

Luminaire Tested: P3AS05R55W2N902765DE010 E3DL1LI\_3500K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1290505  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R55W2N902765DE010 E3DL1LI\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3500K CCT AND, 90CRI ,  
E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 437.9 lumens  
Efficiency: N/A  
Efficacy: 74.2 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1290505

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DL1LI\_3500K

### Luminous Intensity Polar Plot



TEST NUMBER: P1290505

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DL1LI\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |  | 100 |
| 1   | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 |  | 101 | 99  | 98  |  | 97  | 96  | 95  |  | 93  |
| 2   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 94  | 98  | 95  | 92  |  | 95  | 92  | 90  |  | 92  | 90  | 88  |  | 87  |
| 3   | 102 | 96  | 91  | 87  | 100 | 95  | 90  | 86  | 92  | 88  | 85  |  | 89  | 86  | 84  |  | 87  | 85  | 82  |  | 81  |
| 4   | 97  | 90  | 84  | 80  | 95  | 89  | 83  | 79  | 86  | 82  | 78  |  | 84  | 81  | 78  |  | 82  | 79  | 77  |  | 75  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 78  | 74  | 81  | 77  | 73  |  | 80  | 76  | 72  |  | 78  | 75  | 72  |  | 70  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 73  | 68  | 77  | 72  | 68  |  | 75  | 71  | 68  |  | 74  | 70  | 67  |  | 66  |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  |  | 71  | 67  | 63  |  | 70  | 66  | 63  |  | 62  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 63  | 60  |  | 67  | 63  | 60  |  | 67  | 62  | 59  |  | 58  |
| 9   | 76  | 66  | 61  | 57  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 56  |  | 63  | 59  | 56  |  | 55  |
| 10  | 73  | 63  | 57  | 53  | 72  | 62  | 57  | 53  | 62  | 57  | 53  |  | 61  | 56  | 53  |  | 60  | 56  | 53  |  | 52  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 120275 |
| 5°  | 119040 |
| 10° | 114961 |
| 15° | 106266 |
| 20° | 91708  |
| 25° | 72440  |
| 30° | 51375  |
| 35° | 33140  |
| 40° | 19894  |
| 45° | 11226  |
| 50° | 6038   |
| 55° | 2141   |
| 60° | 1930   |
| 65° | 1868   |
| 70° | 1795   |
| 75° | 1694   |
| 80° | 1515   |
| 85° | 1006   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11226 cd/sqm

TEST NUMBER: P1290505

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DL1LI\_3500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 50.9   | 11.6      |
| 10°-20°   | 129.4  | 29.6      |
| 20°-30°   | 135.7  | 31.0      |
| 30°-40°   | 79.1   | 18.1      |
| 40°-50°   | 29.6   | 6.8       |
| 50°-60°   | 6.9    | 1.6       |
| 60°-70°   | 3.6    | 0.8       |
| 70°-80°   | 2.1    | 0.5       |
| 80°-90°   | 0.6    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 316.0  | 72.1      |
| 0°-40°    | 395.1  | 90.2      |
| 0°-60°    | 431.7  | 98.6      |
| 0°-90°    | 437.9  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 437.9  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 548 |      |
| 5°  | 541 | 51   |
| 15° | 468 | 129  |
| 25° | 299 | 136  |
| 35° | 124 | 79   |
| 45° | 36  | 30   |
| 55° | 6   | 7    |
| 65° | 4   | 4    |
| 75° | 2   | 2    |
| 85° | 0   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1290505

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DL1LI\_3500K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 548.5 |
| 2.5°  | 546.9 |
| 5°    | 540.8 |
| 7.5°  | 531.2 |
| 10°   | 516.3 |
| 12.5° | 495.4 |
| 15°   | 468.1 |
| 17.5° | 433.6 |
| 20°   | 393.0 |
| 22.5° | 347.6 |
| 25°   | 299.4 |
| 27.5° | 249.9 |
| 30°   | 202.9 |
| 32.5° | 160.3 |
| 35°   | 123.8 |
| 37.5° | 94.0  |
| 40°   | 69.5  |
| 42.5° | 49.8  |
| 45°   | 36.2  |
| 47.5° | 26.1  |
| 50°   | 17.7  |
| 52.5° | 10.0  |
| 55°   | 5.6   |
| 57.5° | 4.8   |
| 60°   | 4.4   |
| 62.5° | 4.0   |
| 65°   | 3.6   |
| 67.5° | 3.2   |
| 70°   | 2.8   |
| 72.5° | 2.4   |
| 75°   | 2.0   |
| 77.5° | 1.6   |
| 80°   | 1.2   |
| 82.5° | 0.8   |
| 85°   | 0.4   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)