

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288125

Luminaire Tested: P3AS05R20W2N902750DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R20W2N902750DE010 E3DL1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 201.0 lumens
Efficiency: N/A
Efficacy: 34.1 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288125
CATALOG NUMBER: P3AS05R20W2N902750DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1288125

CATALOG NUMBER: P3AS05R20W2N902750DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	154637
5°	140568
10°	103895
15°	64268
20°	36707
25°	20953
30°	11749
35°	6398
40°	3492
45°	1923
50°	1126
55°	803
60°	746
65°	726
70°	641
75°	678
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1923 cd/sqm



TEST NUMBER: P1288125
 CATALOG NUMBER: P3AS05R20W2N902750DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.3	27.5
10°-20°	78.9	39.3
20°-30°	41.2	20.5
30°-40°	15.9	7.9
40°-50°	5.2	2.6
50°-60°	2.0	1.0
60°-70°	1.4	0.7
70°-80°	0.8	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	175.5	87.3
0°-40°	191.4	95.2
0°-60°	198.6	98.8
0°-90°	201.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	201.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	705	
5°	639	55
15°	283	79
25°	87	41
35°	24	16
45°	6	5
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1288125
CATALOG NUMBER: P3AS05R20W2N902750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	705.2
1°	703.9
2°	695.5
3°	682.7
4°	662.9
5°	638.6
6°	609.9
7°	578.1
8°	541.2
9°	505.2
10°	466.6
12.5°	370.9
15°	283.1
17.5°	211.8
20°	157.3
22.5°	116.5
25°	86.6
27.5°	63.9
30°	46.4
32.5°	33.6
35°	23.9
37.5°	17.3
40°	12.2
42.5°	8.7
45°	6.2
47.5°	4.5
50°	3.3
52.5°	2.5
55°	2.1
57.5°	1.9
60°	1.7
62.5°	1.6
65°	1.4
67.5°	1.2
70°	1.0
72.5°	1.0
75°	0.8
77.5°	0.6
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)