

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288149

Luminaire Tested: P3AS05R20W2N902750DE010 E3DLD1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R20W2N902750DE010 E3DLD1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 138.0 lumens
Efficiency: N/A
Efficacy: 23.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288149
CATALOG NUMBER: P3AS05R20W2N902750DE010 E3DLD1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1288149
 CATALOG NUMBER: P3AS05R20W2N902750DE010 E3DLD1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91	91	91	91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83	83	83	83
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55	55	55	55
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52	52	52	52
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48	48	48	48
10	68	58	51	47	67	57	51	47	56	51	47	56	50	47	55	50	47	45	45	45	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34142
5°	33216
10°	30572
15°	26901
20°	23079
25°	19380
30°	15673
35°	11912
40°	8473
45°	5613
50°	3480
55°	2294
60°	2061
65°	1920
70°	1795
75°	1610
80°	1515
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5613 cd/sqm



TEST NUMBER: P1288149

CATALOG NUMBER: P3AS05R20W2N902750DE010 E3DLD1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.0	10.1
10°-20°	33.0	23.9
20°-30°	36.6	26.5
30°-40°	27.9	20.2
40°-50°	14.3	10.4
50°-60°	5.9	4.3
60°-70°	3.7	2.7
70°-80°	2.1	1.5
80°-90°	0.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	83.6	60.6
0°-40°	111.5	80.8
0°-60°	131.7	95.4
0°-90°	138.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	138.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	156	
5°	151	14
15°	118	33
25°	80	37
35°	44	28
45°	18	14
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1288149
CATALOG NUMBER: P3AS05R20W2N902750DE010 E3DLD1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	155.7
1°	155.8
2°	155.1
3°	154.3
4°	152.9
5°	150.9
6°	148.7
7°	146.2
8°	143.6
9°	140.4
10°	137.3
12.5°	128.1
15°	118.5
17.5°	108.7
20°	98.9
22.5°	89.1
25°	80.1
27.5°	71.2
30°	61.9
32.5°	53.1
35°	44.5
37.5°	37.0
40°	29.6
42.5°	23.3
45°	18.1
47.5°	13.7
50°	10.2
52.5°	7.5
55°	6.0
57.5°	5.4
60°	4.7
62.5°	4.2
65°	3.7
67.5°	3.2
70°	2.8
72.5°	2.3
75°	1.9
77.5°	1.6
80°	1.2
82.5°	0.9
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)