

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290518

Luminaire Tested: P3AS05R55W2N902765DE010 E3DL1WH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290518
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R55W2N902765DE010 E3DL1WH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 4000K CCT AND, 90CRI ,
E3DL1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 292.0 lumens
Efficiency: N/A
Efficacy: 49.5 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290518

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DL1WH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1290518

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DL1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		97	95	94		92			
2	107	102	97	94		105	100	96	93		97	93	91		94	91	89		91	89	87		85			
3	101	94	89	85		99	93	88	84		90	86	83		88	84	81		85	83	80		79			
4	96	88	82	77		94	87	81	77		84	80	76		82	78	75		80	77	74		73			
5	91	82	76	71		89	81	75	71		79	74	70		77	73	70		76	72	69		67			
6	86	77	70	66		84	76	70	66		74	69	65		73	68	65		72	68	64		63			
7	82	72	66	61		80	71	65	61		70	65	61		69	64	60		68	63	60		59			
8	78	68	62	57		76	67	61	57		66	61	57		65	60	57		64	60	56		55			
9	74	64	58	54		73	63	58	54		62	57	53		62	57	53		61	56	53		52			
10	70	60	55	51		69	60	54	50		59	54	50		58	54	50		58	53	50		49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79423
5°	77438
10°	71987
15°	64109
20°	54488
25°	43962
30°	33524
35°	23851
40°	15744
45°	9334
50°	5458
55°	3364
60°	2982
65°	2698
70°	2308
75°	2033
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9334 cd/sqm

TEST NUMBER: P1290518

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DL1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.7	11.2
10°-20°	78.3	26.8
20°-30°	82.9	28.4
30°-40°	56.0	19.2
40°-50°	24.6	8.4
50°-60°	8.8	3.0
60°-70°	5.1	1.8
70°-80°	2.7	0.9
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	193.9	66.4
0°-40°	249.9	85.6
0°-60°	283.3	97.0
0°-90°	292.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	292.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	362	
5°	352	33
15°	282	78
25°	182	83
35°	89	56
45°	30	25
55°	9	9
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1290518

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DL1WH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	362.2
2.5°	359.4
5°	351.8
7.5°	339.4
10°	323.3
12.5°	304.1
15°	282.4
17.5°	258.3
20°	233.5
22.5°	207.4
25°	181.7
27.5°	156.5
30°	132.4
32.5°	109.5
35°	89.1
37.5°	70.6
40°	55.0
42.5°	41.3
45°	30.1
47.5°	22.1
50°	16.0
52.5°	11.2
55°	8.8
57.5°	8.0
60°	6.8
62.5°	6.0
65°	5.2
67.5°	4.4
70°	3.6
72.5°	3.2
75°	2.4
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)