

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290534

Luminaire Tested: P3AS05R55W2N902765DE010 E3DLD1H_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290534
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R55W2N902765DE010 E3DLD1H_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,
E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 335.0 lumens
Efficiency: N/A
Efficacy: 56.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290534
CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLD1H_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1290534
 CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLD1H_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82		
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74		
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68		
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62		
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57		
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52		
8	73	62	55	51	72	62	55	51	60	54	50	59	54	50	58	53	50	48		
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45		
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62999
5°	62183
10°	59741
15°	55869
20°	50964
25°	45462
30°	39778
35°	33033
40°	26049
45°	17676
50°	10814
55°	5582
60°	5219
65°	4929
70°	4552
75°	3982
80°	4041
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17676 cd/sqm



TEST NUMBER: P1290534

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLD1H_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.5	7.9
10°-20°	68.8	20.5
20°-30°	86.1	25.7
30°-40°	76.9	22.9
40°-50°	45.0	13.4
50°-60°	15.6	4.6
60°-70°	9.4	2.8
70°-80°	5.2	1.6
80°-90°	1.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	181.4	54.1
0°-40°	258.3	77.1
0°-60°	318.9	95.2
0°-90°	335.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	335.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	287	
5°	282	26
15°	246	69
25°	188	86
35°	123	77
45°	57	45
55°	15	16
65°	10	9
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P1290534
CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLD1H_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	287.3
2.5°	285.7
5°	282.5
7.5°	276.2
10°	268.3
12.5°	258.4
15°	246.1
17.5°	233.0
20°	218.4
22.5°	203.4
25°	187.9
27.5°	172.5
30°	157.1
32.5°	140.5
35°	123.4
37.5°	106.8
40°	91.0
42.5°	74.0
45°	57.0
47.5°	43.5
50°	31.7
52.5°	20.6
55°	14.6
57.5°	13.1
60°	11.9
62.5°	10.7
65°	9.5
67.5°	8.3
70°	7.1
72.5°	5.9
75°	4.7
77.5°	4.0
80°	3.2
82.5°	2.0
85°	1.2
87.5°	0.8
90°	0.0

(END OF REPORT)