

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290557

Luminaire Tested: P3AS05R55W2N902765DE010 E3DLD1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290557
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R55W2N902765DE010 E3DLD1WMH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 303.0 lumens
Efficiency: N/A
Efficacy: 51.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290557
CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLD1WMH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1290557

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLD1WMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56969
5°	56240
10°	54018
15°	50534
20°	46087
25°	41131
30°	35980
35°	29901
40°	23558
45°	15971
50°	9757
55°	5046
60°	4693
65°	4462
70°	4103
75°	3643
80°	3662
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15971 cd/sqm



TEST NUMBER: P1290557

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLD1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.0	7.9
10°-20°	62.2	20.5
20°-30°	77.9	25.7
30°-40°	69.5	23.0
40°-50°	40.7	13.4
50°-60°	14.0	4.6
60°-70°	8.5	2.8
70°-80°	4.7	1.6
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	164.1	54.2
0°-40°	233.6	77.1
0°-60°	288.4	95.2
0°-90°	303.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	303.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	260	
5°	256	24
15°	223	62
25°	170	78
35°	112	70
45°	52	41
55°	13	14
65°	9	8
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1290557
CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLD1WMH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	259.8
2.5°	258.4
5°	255.5
7.5°	249.8
10°	242.6
12.5°	233.7
15°	222.6
17.5°	210.8
20°	197.5
22.5°	183.9
25°	170.0
27.5°	156.0
30°	142.1
32.5°	127.0
35°	111.7
37.5°	96.6
40°	82.3
42.5°	66.9
45°	51.5
47.5°	39.4
50°	28.6
52.5°	18.6
55°	13.2
57.5°	11.8
60°	10.7
62.5°	9.7
65°	8.6
67.5°	7.5
70°	6.4
72.5°	5.4
75°	4.3
77.5°	3.6
80°	2.9
82.5°	1.8
85°	1.1
87.5°	0.7
90°	0.0

(END OF REPORT)