

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290566

Luminaire Tested: P3AS05R55W2N902765DE010 E3DLP1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290566
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R55W2N902765DE010 E3DLP1GPH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 4000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 143.0 lumens
Efficiency: N/A
Efficacy: 24.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290566

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLP1GPH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1290566

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLP1GPH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92		
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78		
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73		
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55		
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52		
10	70	60	54	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38900
5°	37926
10°	35248
15°	31396
20°	26672
25°	21534
30°	16408
35°	11671
40°	7700
45°	4559
50°	2695
55°	1644
60°	1447
65°	1349
70°	1154
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4559 cd/sqm

TEST NUMBER: P1290566

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLP1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.0	11.2
10°-20°	38.3	26.8
20°-30°	40.6	28.4
30°-40°	27.4	19.2
40°-50°	12.0	8.4
50°-60°	4.3	3.0
60°-70°	2.5	1.8
70°-80°	1.3	0.9
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	94.9	66.4
0°-40°	122.4	85.6
0°-60°	138.7	97.0
0°-90°	143.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	143.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	177	
5°	172	16
15°	138	38
25°	89	41
35°	44	27
45°	15	12
55°	4	4
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1290566

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLP1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	177.4
2.5°	176.0
5°	172.3
7.5°	166.2
10°	158.3
12.5°	148.9
15°	138.3
17.5°	126.5
20°	114.3
22.5°	101.6
25°	89.0
27.5°	76.6
30°	64.8
32.5°	53.6
35°	43.6
37.5°	34.6
40°	26.9
42.5°	20.2
45°	14.7
47.5°	10.8
50°	7.9
52.5°	5.5
55°	4.3
57.5°	3.9
60°	3.3
62.5°	2.9
65°	2.6
67.5°	2.2
70°	1.8
72.5°	1.6
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)