

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288267

Luminaire Tested: P3AS05R20W2N902765DE010 E3DL1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288267
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R20W2N902765DE010 E3DL1GPH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3500K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 204.0 lumens
Efficiency: N/A
Efficacy: 34.6 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288267

CATALOG NUMBER: P3AS05R20W2N902765DE010 E3DL1GPH_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1288267

CATALOG NUMBER: P3AS05R20W2N902765DE010 E3DL1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83		
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79		
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	74	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71		
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68		
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	156961
5°	142681
10°	105453
15°	65222
20°	37243
25°	21267
30°	11926
35°	6478
40°	3550
45°	1954
50°	1160
55°	841
60°	789
65°	726
70°	641
75°	678
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1954 cd/sqm

TEST NUMBER: P1288267

CATALOG NUMBER: P3AS05R20W2N902765DE010 E3DL1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.1	27.5
10°-20°	80.1	39.3
20°-30°	41.8	20.5
30°-40°	16.2	7.9
40°-50°	5.2	2.6
50°-60°	2.1	1.0
60°-70°	1.4	0.7
70°-80°	0.8	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	178.1	87.3
0°-40°	194.2	95.2
0°-60°	201.6	98.8
0°-90°	204.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	204.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	716	
5°	648	56
15°	287	80
25°	88	42
35°	24	16
45°	6	5
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1288267

CATALOG NUMBER: P3AS05R20W2N902765DE010 E3DL1GPH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	715.8
1°	714.4
2°	705.9
3°	692.9
4°	672.8
5°	648.2
6°	619.0
7°	586.7
8°	549.2
9°	512.8
10°	473.6
12.5°	376.4
15°	287.3
17.5°	215.0
20°	159.6
22.5°	118.2
25°	87.9
27.5°	64.8
30°	47.1
32.5°	34.1
35°	24.2
37.5°	17.5
40°	12.4
42.5°	8.9
45°	6.3
47.5°	4.5
50°	3.4
52.5°	2.6
55°	2.2
57.5°	2.0
60°	1.8
62.5°	1.6
65°	1.4
67.5°	1.2
70°	1.0
72.5°	1.0
75°	0.8
77.5°	0.6
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)