

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290568

Luminaire Tested: P3AS05R55W2N902765DE010 E3DLP1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290568
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R55W2N902765DE010 E3DLP1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 6500K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 142.0 lumens
Efficiency: N/A
Efficacy: 24.1 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290568

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLP1GPH_6500K

Luminous Intensity Polar Plot



TEST NUMBER: P1290568

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLP1GPH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		97	95	94
2	107	102	97	94		105	100	96	93		97	93	91		94	91	89		91	89	87
3	101	94	89	85		99	93	88	84		90	86	83		88	84	81		85	83	80
4	96	88	82	77		94	87	81	77		84	80	76		82	78	75		80	77	74
5	91	82	76	71		89	81	75	71		79	74	70		77	73	70		76	72	69
6	86	77	70	66		84	76	70	66		74	69	65		73	68	65		72	67	64
7	82	72	66	61		80	71	65	61		70	65	61		69	64	60		68	63	60
8	78	68	62	57		76	67	61	57		66	61	57		65	60	57		64	60	56
9	74	64	58	54		73	63	58	54		62	57	53		62	57	53		61	56	53
10	70	60	54	51		69	60	54	50		59	54	50		58	54	50		58	53	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38637
5°	37662
10°	35003
15°	31169
20°	26486
25°	21388
30°	16306
35°	11591
40°	7643
45°	4528
50°	2661
55°	1644
60°	1447
65°	1297
70°	1154
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4528 cd/sqm

TEST NUMBER: P1290568

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLP1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.9	11.2
10°-20°	38.1	26.8
20°-30°	40.3	28.4
30°-40°	27.2	19.2
40°-50°	11.9	8.4
50°-60°	4.3	3.0
60°-70°	2.5	1.7
70°-80°	1.3	0.9
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	94.3	66.4
0°-40°	121.5	85.6
0°-60°	137.7	97.0
0°-90°	142.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	142.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	176	
5°	171	16
15°	137	38
25°	88	40
35°	43	27
45°	15	12
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1290568

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLP1GPH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	176.2
2.5°	174.8
5°	171.1
7.5°	165.0
10°	157.2
12.5°	147.9
15°	137.3
17.5°	125.6
20°	113.5
22.5°	100.9
25°	88.4
27.5°	76.1
30°	64.4
32.5°	53.3
35°	43.3
37.5°	34.3
40°	26.7
42.5°	20.1
45°	14.6
47.5°	10.7
50°	7.8
52.5°	5.5
55°	4.3
57.5°	3.9
60°	3.3
62.5°	2.9
65°	2.5
67.5°	2.1
70°	1.8
72.5°	1.6
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)