

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290633

Luminaire Tested: P3AS05R60W2N902750DE010 E3D1H\_5000K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1290633  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R60W2N902750DE010 E3D1H\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 478.0 lumens  
Efficiency: N/A  
Efficacy: 81.0 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1290633

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3D1H\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1290633

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3D1H\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 102 |  | 101 | 100 | 99  |  | 98  |
| 2   | 108 | 104 | 100 | 96  | 106 | 102 | 98  | 95  | 99  | 96  | 93  |  | 96  | 93  | 91  |  | 93  |
| 3   | 103 | 97  | 92  | 88  | 101 | 96  | 91  | 88  | 93  | 89  | 86  |  | 91  | 87  | 85  |  | 88  |
| 4   | 98  | 91  | 85  | 81  | 96  | 90  | 85  | 81  | 88  | 83  | 80  |  | 86  | 82  | 79  |  | 84  |
| 5   | 93  | 85  | 80  | 75  | 92  | 84  | 79  | 75  | 83  | 78  | 74  |  | 81  | 77  | 74  |  | 79  |
| 6   | 89  | 80  | 74  | 70  | 87  | 79  | 74  | 70  | 78  | 73  | 70  |  | 77  | 72  | 69  |  | 75  |
| 7   | 85  | 76  | 70  | 66  | 83  | 75  | 69  | 65  | 74  | 69  | 65  |  | 72  | 68  | 65  |  | 71  |
| 8   | 81  | 71  | 65  | 61  | 79  | 71  | 65  | 61  | 70  | 65  | 61  |  | 69  | 64  | 61  |  | 68  |
| 9   | 77  | 67  | 62  | 58  | 76  | 67  | 61  | 58  | 66  | 61  | 57  |  | 65  | 61  | 57  |  | 64  |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  | 63  | 58  | 54  |  | 62  | 57  | 54  |  | 61  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 125253 |
| 5°  | 118226 |
| 10° | 115162 |
| 15° | 112532 |
| 20° | 104636 |
| 25° | 93538  |
| 30° | 71454  |
| 35° | 41251  |
| 40° | 16001  |
| 45° | 6667   |
| 50° | 1467   |
| 55° | 229    |
| 60° | 175    |
| 65° | 104    |
| 70° | 128    |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6667 cd/sqm

TEST NUMBER: P1290633

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3D1H\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 50.7   | 10.6      |
| 10°-20°   | 138.1  | 28.9      |
| 20°-30°   | 172.9  | 36.2      |
| 30°-40°   | 96.7   | 20.2      |
| 40°-50°   | 18.4   | 3.8       |
| 50°-60°   | 1.0    | 0.2       |
| 60°-70°   | 0.2    | 0.0       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 361.7  | 75.7      |
| 0°-40°    | 458.4  | 95.9      |
| 0°-60°    | 477.7  | 99.9      |
| 0°-90°    | 478.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 478.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 571 |      |
| 5°  | 537 | 51   |
| 15° | 496 | 138  |
| 25° | 387 | 173  |
| 35° | 154 | 97   |
| 45° | 22  | 18   |
| 55° | 1   | 1    |
| 65° | 0   | 0    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1290633

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3D1H\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 571.2 |
| 1°    | 568.8 |
| 2°    | 561.4 |
| 3°    | 552.6 |
| 4°    | 544.4 |
| 5°    | 537.1 |
| 6°    | 531.7 |
| 7°    | 527.0 |
| 8°    | 523.4 |
| 9°    | 520.1 |
| 10°   | 517.2 |
| 11°   | 514.3 |
| 12°   | 510.9 |
| 13°   | 506.8 |
| 14°   | 501.9 |
| 15°   | 495.7 |
| 16°   | 488.1 |
| 17°   | 479.4 |
| 18°   | 469.7 |
| 19°   | 458.5 |
| 20°   | 448.4 |
| 21°   | 437.4 |
| 22°   | 426.1 |
| 23°   | 414.1 |
| 24°   | 401.0 |
| 25°   | 386.6 |
| 26°   | 369.6 |
| 27°   | 350.6 |
| 28°   | 329.3 |
| 29°   | 306.6 |
| 30°   | 282.2 |
| 31°   | 257.5 |
| 32°   | 232.1 |
| 32.5° | 218.2 |
| 33°   | 205.7 |
| 34°   | 179.7 |
| 35°   | 154.1 |
| 36°   | 131.0 |
| 37°   | 106.6 |
| 37.5° | 95.4  |
| 38°   | 84.5  |
| 39°   | 68.0  |
| 40°   | 55.9  |
| 42.5° | 34.0  |
| 45°   | 21.5  |



TEST NUMBER: P1290633

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3D1H\_5000K

**CANDELA DISTRIBUTION (continued):**

|       | 0°   |
|-------|------|
| 47.5° | 11.9 |
| 50°   | 4.3  |
| 52.5° | 1.0  |
| 55°   | 0.6  |
| 57.5° | 0.4  |
| 60°   | 0.4  |
| 62.5° | 0.2  |
| 65°   | 0.2  |
| 67.5° | 0.2  |
| 70°   | 0.2  |
| 72.5° | 0.2  |
| 75°   | 0.0  |
| 77.5° | 0.0  |
| 80°   | 0.0  |
| 82.5° | 0.0  |
| 85°   | 0.0  |
| 87.5° | 0.0  |
| 90°   | 0.0  |

(END OF REPORT)