

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290705

Luminaire Tested: P3AS05R60W2N902750DE010 E3DLD1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290705
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R60W2N902750DE010 E3DLD1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 326.0 lumens
Efficiency: N/A
Efficacy: 55.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290705

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3DLD1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1290705

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3DLD1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91						
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82						
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74						
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67						
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61						
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56						
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51						
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47						
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44						
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57868
5°	57231
10°	55243
15°	52191
20°	48094
25°	43551
30°	38664
35°	33033
40°	26278
45°	18514
50°	11053
55°	5582
60°	5394
65°	4929
70°	4552
75°	4321
80°	4041
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18514 cd/sqm

TEST NUMBER: P1290705

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3DLD1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.4	7.5
10°-20°	64.2	19.7
20°-30°	82.5	25.3
30°-40°	76.5	23.5
40°-50°	46.6	14.3
50°-60°	15.5	4.8
60°-70°	9.4	2.9
70°-80°	5.3	1.6
80°-90°	1.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	171.2	52.5
0°-40°	247.6	76.0
0°-60°	309.7	95.0
0°-90°	326.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	326.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	264	
5°	260	24
15°	230	64
25°	180	82
35°	123	76
45°	60	47
55°	15	16
65°	10	9
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P1290705

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3DLD1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	263.9
2.5°	262.7
5°	260.0
7.5°	254.8
10°	248.1
12.5°	239.8
15°	229.9
17.5°	218.4
20°	206.1
22.5°	193.1
25°	180.0
27.5°	166.6
30°	152.7
32.5°	138.9
35°	123.4
37.5°	107.2
40°	91.8
42.5°	75.6
45°	59.7
47.5°	46.3
50°	32.4
52.5°	19.4
55°	14.6
57.5°	13.5
60°	12.3
62.5°	10.7
65°	9.5
67.5°	8.3
70°	7.1
72.5°	5.9
75°	5.1
77.5°	4.0
80°	3.2
82.5°	2.0
85°	1.2
87.5°	0.8
90°	0.0

(END OF REPORT)