

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290773

Luminaire Tested: P3AS05R60W2N902765DE010 E3CD1MMS_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290773
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R60W2N902765DE010 E3CD1MMS_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 6500K CCT AND, 90CRI ,
E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 516.0 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290773

CATALOG NUMBER: P3AS05R60W2N902765DE010 E3CD1MMS_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1290773

CATALOG NUMBER: P3AS05R60W2N902765DE010 E3CD1MMS_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	114	111	108	106		111	109	106	104		105	103	101		101	100	98		97	96	95		94			
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89		87			
3	103	96	91	88		101	95	90	87		92	89	85		90	87	84		88	85	83		81			
4	98	90	85	81		96	89	84	80		87	83	79		85	81	78		83	80	77		76			
5	93	84	79	74		91	84	78	74		82	77	73		80	76	73		79	75	72		71			
6	88	79	73	69		87	79	73	69		77	72	68		76	71	68		74	70	68		66			
7	84	75	69	64		82	74	68	64		73	68	64		71	67	64		70	66	63		62			
8	80	70	64	60		78	70	64	60		69	64	60		68	63	60		67	62	59		58			
9	76	66	61	57		75	66	60	56		65	60	56		64	59	56		63	59	56		55			
10	72	63	57	53		71	62	57	53		62	56	53		61	56	53		60	56	53		51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123214
5°	118336
10°	121841
15°	123406
20°	108953
25°	91820
30°	74467
35°	48506
40°	22270
45°	8528
50°	2866
55°	765
60°	702
65°	623
70°	513
75°	678
80°	505
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8528 cd/sqm

TEST NUMBER: P1290773

CATALOG NUMBER: P3AS05R60W2N902765DE010 E3CD1MMS_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.7	10.0
10°-20°	148.8	28.8
20°-30°	173.6	33.6
30°-40°	112.0	21.7
40°-50°	25.1	4.9
50°-60°	2.5	0.5
60°-70°	1.2	0.2
70°-80°	0.7	0.1
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	374.2	72.5
0°-40°	486.2	94.2
0°-60°	513.9	99.6
0°-90°	516.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	516.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	562	
5°	538	52
15°	544	149
25°	380	174
35°	181	112
45°	28	25
55°	2	3
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1290773

CATALOG NUMBER: P3AS05R60W2N902765DE010 E3CD1MMS_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	561.9
2.5°	552.7
5°	537.6
7.5°	536.8
10°	547.2
12.5°	553.9
15°	543.6
17.5°	512.4
20°	466.9
22.5°	419.4
25°	379.5
27.5°	340.4
30°	294.1
32.5°	239.9
35°	181.2
37.5°	123.7
40°	77.8
42.5°	46.7
45°	27.5
47.5°	16.0
50°	8.4
52.5°	2.8
55°	2.0
57.5°	1.6
60°	1.6
62.5°	1.2
65°	1.2
67.5°	1.2
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)