

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290954

Luminaire Tested: P3AS05R65W2N902750DE010 E3D1LI_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290954
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65W2N902750DE010 E3D1LI_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 472.0 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290954

CATALOG NUMBER: P3AS05R65W2N902750DE010 E3D1LI_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1290954

CATALOG NUMBER: P3AS05R65W2N902750DE010 E3D1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	70	65	83	75	69	65	73	69	65		72	68	65		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	126481
5°	117433
10°	113558
15°	109444
20°	101182
25°	92183
30°	71226
35°	41278
40°	16374
45°	6977
50°	1672
55°	229
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6977 cd/sqm

TEST NUMBER: P1290954

CATALOG NUMBER: P3AS05R65W2N902750DE010 E3D1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.3	10.7
10°-20°	134.3	28.5
20°-30°	170.0	36.0
30°-40°	96.8	20.5
40°-50°	19.2	4.1
50°-60°	1.0	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	354.7	75.1
0°-40°	451.5	95.6
0°-60°	471.7	99.9
0°-90°	472.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	472.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	577	
5°	534	50
15°	482	134
25°	381	170
35°	154	97
45°	22	19
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1290954

CATALOG NUMBER: P3AS05R65W2N902750DE010 E3D1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	576.8
1°	572.5
2°	563.2
3°	552.3
4°	541.7
5°	533.5
6°	527.5
7°	522.6
8°	518.4
9°	514.1
10°	510.0
11°	505.6
12°	500.9
13°	495.3
14°	489.3
15°	482.1
16°	473.6
17°	464.3
18°	454.2
19°	443.5
20°	433.6
21°	423.5
22°	414.4
23°	404.9
24°	393.8
25°	381.0
26°	365.7
27°	347.3
28°	326.5
29°	304.4
30°	281.3
31°	255.9
32°	230.7
32.5°	217.7
33°	205.1
34°	179.5
35°	154.2
36°	131.0
37°	107.9
37.5°	96.0
38°	86.5
39°	70.0
40°	57.2
42.5°	35.3
45°	22.5



TEST NUMBER: P1290954

CATALOG NUMBER: P3AS05R65W2N902750DE010 E3D1LI_3000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	13.2
50°	4.9
52.5°	1.0
55°	0.6
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)