

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288444

Luminaire Tested: P3AS05R25W2N902750DE010 E3DLD1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288444
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25W2N902750DE010 E3DLD1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 157.0 lumens
Efficiency: N/A
Efficacy: 26.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288444

CATALOG NUMBER: P3AS05R25W2N902750DE010 E3DLD1GPH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288444

CATALOG NUMBER: P3AS05R25W2N902750DE010 E3DLD1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37322
5°	36430
10°	33756
15°	30057
20°	25832
25°	21969
30°	18079
35°	14081
40°	10133
45°	6419
50°	3787
55°	2600
60°	2412
65°	2231
70°	1988
75°	1864
80°	1768
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6419 cd/sqm

TEST NUMBER: P1288444

CATALOG NUMBER: P3AS05R25W2N902750DE010 E3DLD1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.3	9.8
10°-20°	36.8	23.4
20°-30°	41.5	26.5
30°-40°	32.8	20.9
40°-50°	16.6	10.6
50°-60°	6.6	4.2
60°-70°	4.3	2.7
70°-80°	2.4	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	93.6	59.6
0°-40°	126.5	80.6
0°-60°	149.7	95.4
0°-90°	157.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	157.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	170	
5°	166	15
15°	132	37
25°	91	42
35°	53	33
45°	21	17
55°	7	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1288444

CATALOG NUMBER: P3AS05R25W2N902750DE010 E3DLD1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	170.2
1°	170.2
2°	169.6
3°	168.6
4°	167.2
5°	165.5
6°	163.3
7°	160.8
8°	158.0
9°	154.9
10°	151.6
11°	147.9
12°	144.3
13°	140.2
14°	136.3
15°	132.4
17.5°	121.5
20°	110.7
22.5°	100.5
25°	90.8
27.5°	81.2
30°	71.4
32.5°	62.2
35°	52.6
37.5°	43.8
40°	35.4
42.5°	27.6
45°	20.7
47.5°	15.5
50°	11.1
52.5°	8.4
55°	6.8
57.5°	6.3
60°	5.5
62.5°	4.9
65°	4.3
67.5°	3.7
70°	3.1
72.5°	2.7
75°	2.2
77.5°	1.8
80°	1.4
82.5°	1.0
85°	0.6
87.5°	0.2



TEST NUMBER: P1288444

CATALOG NUMBER: P3AS05R25W2N902750DE010 E3DLD1GPH_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)