

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288466

Luminaire Tested: P3AS05R25W2N902750DE010 E3DLD1WMH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1288466  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R25W2N902750DE010 E3DLD1WMH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,  
E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 317.0 lumens  
Efficiency: N/A  
Efficacy: 53.7 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1288466  
CATALOG NUMBER: P3AS05R25W2N902750DE010 E3DLD1WMH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1288466

CATALOG NUMBER: P3AS05R25W2N902750DE010 E3DLD1WMH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	75345
5°	73542
10°	68157
15°	60704
20°	52155
25°	44325
30°	36487
35°	28429
40°	20467
45°	12994
50°	7676
55°	5276
60°	4868
65°	4514
70°	4039
75°	3643
80°	3536
85°	3019

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12994 cd/sqm



TEST NUMBER: P1288466

CATALOG NUMBER: P3AS05R25W2N902750DE010 E3DLD1WMH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	31.0	9.8
10°-20°	74.2	23.4
20°-30°	83.9	26.5
30°-40°	66.3	20.9
40°-50°	33.5	10.6
50°-60°	13.4	4.2
60°-70°	8.6	2.7
70°-80°	4.7	1.5
80°-90°	1.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	189.1	59.6
0°-40°	255.4	80.6
0°-60°	302.3	95.4
0°-90°	317.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	317.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	344	
5°	334	31
15°	267	74
25°	183	84
35°	106	66
45°	42	34
55°	14	13
65°	9	9
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1288466  
CATALOG NUMBER: P3AS05R25W2N902750DE010 E3DLD1WMH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	343.6
1°	343.6
2°	342.4
3°	340.4
4°	337.7
5°	334.1
6°	329.8
7°	324.6
8°	319.1
9°	312.8
10°	306.1
11°	298.6
12°	291.4
13°	283.2
14°	275.3
15°	267.4
17.5°	245.2
20°	223.5
22.5°	203.0
25°	183.2
27.5°	163.9
30°	144.1
32.5°	125.6
35°	106.2
37.5°	88.5
40°	71.5
42.5°	55.7
45°	41.9
47.5°	31.2
50°	22.5
52.5°	17.0
55°	13.8
57.5°	12.6
60°	11.1
62.5°	9.9
65°	8.7
67.5°	7.5
70°	6.3
72.5°	5.5
75°	4.3
77.5°	3.6
80°	2.8
82.5°	2.0
85°	1.2
87.5°	0.4



TEST NUMBER: P1288466  
CATALOG NUMBER: P3AS05R25W2N902750DE010 E3DLD1WMH\_3000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)