

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291118

Luminaire Tested: P3AS05R65W2N902765DE010 E3D1WH_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291118
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65W2N902765DE010 E3D1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 472.0 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291118
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3D1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1291118
 CATALOG NUMBER: P3AS05R65W2N902765DE010 E3D1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82	82	82	82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77	77	77	77
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67	67	67	67
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63	63	63	63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	126481
5°	117433
10°	113558
15°	109444
20°	101182
25°	92183
30°	71226
35°	41278
40°	16374
45°	6977
50°	1672
55°	229
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6977 cd/sqm



TEST NUMBER: P1291118

CATALOG NUMBER: P3AS05R65W2N902765DE010 E3D1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.3	10.7
10°-20°	134.3	28.5
20°-30°	170.0	36.0
30°-40°	96.8	20.5
40°-50°	19.2	4.1
50°-60°	1.0	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	354.7	75.1
0°-40°	451.5	95.6
0°-60°	471.7	99.9
0°-90°	472.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	472.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	577	
5°	534	50
15°	482	134
25°	381	170
35°	154	97
45°	22	19
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1291118
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3D1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	576.8
1°	572.5
2°	563.2
3°	552.3
4°	541.7
5°	533.5
6°	527.5
7°	522.6
8°	518.4
9°	514.1
10°	510.0
11°	505.6
12°	500.9
13°	495.3
14°	489.3
15°	482.1
16°	473.6
17°	464.3
18°	454.2
19°	443.5
20°	433.6
21°	423.5
22°	414.4
23°	404.9
24°	393.8
25°	381.0
26°	365.7
27°	347.3
28°	326.5
29°	304.4
30°	281.3
31°	255.9
32°	230.7
32.5°	217.7
33°	205.1
34°	179.5
35°	154.2
36°	131.0
37°	107.9
37.5°	96.0
38°	86.5
39°	70.0
40°	57.2
42.5°	35.3
45°	22.5



TEST NUMBER: P1291118
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3D1WH_3000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	13.2
50°	4.9
52.5°	1.0
55°	0.6
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)