

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288514

Luminaire Tested: P3AS05R25W2N902750DE010 E3PHLP1MW_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288514
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25W2N902750DE010 E3PHLP1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,
E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 230.0 lumens
Efficiency: N/A
Efficacy: 39.0 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288514

CATALOG NUMBER: P3AS05R25W2N902750DE010 E3PHLP1MW_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288514

CATALOG NUMBER: P3AS05R25W2N902750DE010 E3PHLP1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68		
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63		
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59		
7	79	69	63	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55		
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52		
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49		
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77275
5°	73013
10°	62056
15°	49149
20°	37360
25°	27873
30°	20256
35°	14348
40°	9733
45°	6791
50°	5697
55°	5505
60°	5789
65°	5967
70°	5898
75°	6354
80°	7324
85°	7296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 82.5°
Luminance: 7728 cd/sqm

TEST NUMBER: P1288514

CATALOG NUMBER: P3AS05R25W2N902750DE010 E3PHLP1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.9	13.0
10°-20°	59.9	26.1
20°-30°	53.1	23.1
30°-40°	33.8	14.7
40°-50°	17.9	7.8
50°-60°	13.1	5.7
60°-70°	11.2	4.9
70°-80°	7.9	3.4
80°-90°	3.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	142.9	62.1
0°-40°	176.7	76.8
0°-60°	207.7	90.3
0°-90°	230.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	230.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	352	
5°	332	30
15°	216	60
25°	115	53
35°	54	34
45°	22	18
55°	14	13
65°	12	11
75°	8	8
85°	3	3
90°	0	

TEST NUMBER: P1288514

CATALOG NUMBER: P3AS05R25W2N902750DE010 E3PHLP1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	352.4
2.5°	347.2
5°	331.7
7.5°	307.5
10°	278.7
12.5°	247.6
15°	216.5
17.5°	186.6
20°	160.1
22.5°	135.9
25°	115.2
27.5°	96.7
30°	80.0
32.5°	65.6
35°	53.6
37.5°	42.6
40°	34.0
42.5°	27.1
45°	21.9
47.5°	19.0
50°	16.7
52.5°	15.5
55°	14.4
57.5°	13.8
60°	13.2
62.5°	12.1
65°	11.5
67.5°	10.4
70°	9.2
72.5°	8.6
75°	7.5
77.5°	6.3
80°	5.8
82.5°	4.6
85°	2.9
87.5°	1.2
90°	0.0

(END OF REPORT)