

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288581

Luminaire Tested: P3AS05R25W2N902765DE010 E3DL1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288581
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25W2N902765DE010 E3DL1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 184.1 lumens
Efficiency: N/A
Efficacy: 31.2 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288581

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DL1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1288581

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DL1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90			
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86			
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82			
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78			
6	94	86	81	78	92	86	81	77	84	80	77	83	79	76	82	78	76	75			
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72			
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66			
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	118039
5°	110125
10°	88219
15°	59887
20°	36240
25°	21195
30°	12078
35°	6639
40°	3521
45°	1861
50°	1092
55°	803
60°	702
65°	726
70°	705
75°	593
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1861 cd/sqm

TEST NUMBER: P1288581

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DL1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	24.1
10°-20°	72.5	39.4
20°-30°	41.4	22.5
30°-40°	16.4	8.9
40°-50°	5.0	2.7
50°-60°	2.0	1.1
60°-70°	1.3	0.7
70°-80°	0.8	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	158.4	86.0
0°-40°	174.7	94.9
0°-60°	181.7	98.7
0°-90°	184.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	184.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	538	
5°	500	44
15°	264	73
25°	88	41
35°	25	16
45°	6	5
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1288581

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DL1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	538.3
1°	537.2
2°	532.8
3°	525.1
4°	514.3
5°	500.3
6°	483.7
7°	465.1
8°	443.5
9°	421.3
10°	396.2
11°	371.4
12°	344.1
13°	317.2
14°	289.6
15°	263.8
17.5°	204.5
20°	155.3
22.5°	116.6
25°	87.6
27.5°	64.9
30°	47.7
32.5°	34.5
35°	24.8
37.5°	17.6
40°	12.3
42.5°	8.4
45°	6.0
47.5°	4.2
50°	3.2
52.5°	2.5
55°	2.1
57.5°	1.9
60°	1.6
62.5°	1.4
65°	1.4
67.5°	1.2
70°	1.1
72.5°	0.9
75°	0.7
77.5°	0.5
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.2



TEST NUMBER: P1288581

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DL1GPH_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)