

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291129

Luminaire Tested: P3AS05R65W2N902765DE010 E3DL1GPH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1291129  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R65W2N902765DE010 E3DL1GPH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 176.0 lumens  
Efficiency: N/A  
Efficacy: 29.8 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1291129  
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3DL1GPH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1291129  
 CATALOG NUMBER: P3AS05R65W2N902765DE010 E3DL1GPH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	71	67	64	63			63
7	81	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58			58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48			48

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	41510
5°	41008
10°	39456
15°	36958
20°	33230
25°	28236
30°	22079
35°	15740
40°	10305
45°	6357
50°	3241
55°	1147
60°	1009
65°	986
70°	898
75°	932
80°	884
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6357 cd/sqm



TEST NUMBER: P1291129

CATALOG NUMBER: P3AS05R65W2N902765DE010 E3DL1GPH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	17.5	9.9
10°-20°	45.3	25.7
20°-30°	53.0	30.1
30°-40°	37.0	21.0
40°-50°	16.3	9.3
50°-60°	3.6	2.1
60°-70°	1.8	1.0
70°-80°	1.1	0.6
80°-90°	0.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	115.7	65.8
0°-40°	152.8	86.8
0°-60°	172.7	98.1
0°-90°	176.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	176.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	189	
5°	186	17
15°	163	45
25°	117	53
35°	59	37
45°	20	16
55°	3	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1291129  
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3DL1GPH\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	189.3
2.5°	188.6
5°	186.3
7.5°	182.4
10°	177.2
12.5°	170.7
15°	162.8
17.5°	153.1
20°	142.4
22.5°	130.3
25°	116.7
27.5°	102.3
30°	87.2
32.5°	72.6
35°	58.8
37.5°	46.7
40°	36.0
42.5°	27.2
45°	20.5
47.5°	15.1
50°	9.5
52.5°	4.9
55°	3.0
57.5°	2.6
60°	2.3
62.5°	2.1
65°	1.9
67.5°	1.6
70°	1.4
72.5°	1.2
75°	1.1
77.5°	0.9
80°	0.7
82.5°	0.5
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)