

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288641

Luminaire Tested: P3AS05R25W2N902765DE010 E3DLD1WH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288641
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25W2N902765DE010 E3DLD1WH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 288.0 lumens
Efficiency: N/A
Efficacy: 48.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288641

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLD1WH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1288641

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLD1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				0				0
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91											
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83											
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76											
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70											
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64											
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59											
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55											
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51											
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48											
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68437
5°	66806
10°	61923
15°	55142
20°	47394
25°	40285
30°	33170
35°	25832
40°	18578
45°	11784
50°	6993
55°	4817
60°	4386
65°	4099
70°	3654
75°	3304
80°	3157
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 11784 cd/sqm

TEST NUMBER: P1288641

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLD1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.2	9.8
10°-20°	67.4	23.4
20°-30°	76.2	26.5
30°-40°	60.3	20.9
40°-50°	30.4	10.6
50°-60°	12.2	4.2
60°-70°	7.8	2.7
70°-80°	4.3	1.5
80°-90°	1.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	171.8	59.6
0°-40°	232.0	80.6
0°-60°	274.7	95.4
0°-90°	288.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	288.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	312	
5°	304	28
15°	243	67
25°	166	76
35°	96	60
45°	38	30
55°	13	12
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1288641

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLD1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	312.1
1°	312.1
2°	311.1
3°	309.3
4°	306.8
5°	303.5
6°	299.6
7°	294.9
8°	289.9
9°	284.2
10°	278.1
11°	271.2
12°	264.8
13°	257.3
14°	250.1
15°	242.9
17.5°	222.8
20°	203.1
22.5°	184.4
25°	166.5
27.5°	148.9
30°	131.0
32.5°	114.1
35°	96.5
37.5°	80.4
40°	64.9
42.5°	50.6
45°	38.0
47.5°	28.3
50°	20.5
52.5°	15.4
55°	12.6
57.5°	11.5
60°	10.0
62.5°	9.0
65°	7.9
67.5°	6.8
70°	5.7
72.5°	5.0
75°	3.9
77.5°	3.2
80°	2.5
82.5°	1.8
85°	1.1
87.5°	0.4



TEST NUMBER: P1288641
CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLD1WH_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)