

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291169

Luminaire Tested: P3AS05R65W2N902765DE010 E3DLD1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291169
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65W2N902765DE010 E3DLD1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 154.0 lumens
Efficiency: N/A
Efficacy: 26.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291169
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3DLD1GPH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1291169

CATALOG NUMBER: P3AS05R65W2N902765DE010 E3DLD1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.6	7.5
10°-20°	30.4	19.7
20°-30°	39.0	25.3
30°-40°	36.1	23.4
40°-50°	21.8	14.2
50°-60°	7.4	4.8
60°-70°	4.5	2.9
70°-80°	2.5	1.6
80°-90°	0.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	80.9	52.5
0°-40°	117.1	76.0
0°-60°	146.3	95.0
0°-90°	154.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	154.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	125	
5°	123	12
15°	108	30
25°	85	39
35°	58	36
45°	28	22
55°	7	7
65°	4	4
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1291169
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3DLD1GPH_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	125.0
2.5°	124.4
5°	122.8
7.5°	120.5
10°	117.3
12.5°	113.4
15°	108.5
17.5°	103.3
20°	97.4
22.5°	91.3
25°	85.3
27.5°	78.8
30°	72.2
32.5°	65.5
35°	58.1
37.5°	50.9
40°	43.2
42.5°	35.6
45°	28.2
47.5°	21.3
50°	14.9
52.5°	9.4
55°	7.2
57.5°	6.5
60°	5.9
62.5°	5.1
65°	4.5
67.5°	3.9
70°	3.3
72.5°	2.9
75°	2.3
77.5°	2.0
80°	1.4
82.5°	1.0
85°	0.6
87.5°	0.4
90°	0.0

(END OF REPORT)