

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291184

Luminaire Tested: P3AS05R65W2N902765DE010 E3DLD1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291184
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65W2N902765DE010 E3DLD1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 312.0 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291184
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3DLD1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1291184
 CATALOG NUMBER: P3AS05R65W2N902765DE010 E3DLD1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20						20							20
RC	80					70						30							10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50
RCR																			
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102
1	112	109	106	103		110	107	104	101		102	100	98		99	97	95		95
2	105	99	94	90		103	97	93	89		94	90	87		91	88	85		88
3	99	91	85	80		96	89	84	79		87	82	78		84	80	77		82
4	92	83	77	72		90	82	76	71		80	75	70		78	73	70		76
5	87	77	70	65		85	76	69	65		74	68	64		72	67	63		71
6	82	71	64	59		80	70	64	59		69	63	58		67	62	58		66
7	77	66	59	54		75	65	59	54		64	58	54		63	57	53		61
8	72	61	55	50		71	61	54	50		60	54	49		59	53	49		58
9	68	57	51	46		67	57	50	46		56	50	46		55	49	46		54
10	65	54	47	43		64	53	47	43		52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55522
5°	54765
10°	52927
15°	49921
20°	46041
25°	41809
30°	37018
35°	31507
40°	25076
45°	17707
50°	10268
55°	5620
60°	5219
65°	4722
70°	4296
75°	4067
80°	3536
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17707 cd/sqm



TEST NUMBER: P1291184

CATALOG NUMBER: P3AS05R65W2N902765DE010 E3DLD1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.4	7.5
10°-20°	61.5	19.7
20°-30°	79.1	25.3
30°-40°	73.1	23.4
40°-50°	44.2	14.2
50°-60°	15.1	4.8
60°-70°	9.1	2.9
70°-80°	5.1	1.6
80°-90°	1.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	164.0	52.6
0°-40°	237.1	76.0
0°-60°	296.4	95.0
0°-90°	312.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	312.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	253	
5°	249	23
15°	220	62
25°	173	79
35°	118	73
45°	57	44
55°	15	15
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1291184
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3DLD1MW_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	253.2
2.5°	252.0
5°	248.8
7.5°	244.1
10°	237.7
12.5°	229.8
15°	219.9
17.5°	209.2
20°	197.3
22.5°	185.0
25°	172.8
27.5°	159.7
30°	146.2
32.5°	132.7
35°	117.7
37.5°	103.0
40°	87.6
42.5°	72.1
45°	57.1
47.5°	43.2
50°	30.1
52.5°	19.0
55°	14.7
57.5°	13.1
60°	11.9
62.5°	10.3
65°	9.1
67.5°	7.9
70°	6.7
72.5°	5.9
75°	4.8
77.5°	4.0
80°	2.8
82.5°	2.0
85°	1.2
87.5°	0.8
90°	0.0

(END OF REPORT)