

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288656

Luminaire Tested: P3AS05R25W2N902765DE010 E3DLP1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288656
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25W2N902765DE010 E3DLP1GPH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 126.1 lumens
Efficiency: N/A
Efficacy: 21.4 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288656

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLP1GPH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288656

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLP1GPH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75
5	92	84	78	74	90	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65	65	65
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	64	60	57	64	59	56	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45742
5°	43892
10°	38454
15°	30897
20°	23755
25°	17977
30°	12989
35°	8620
40°	5238
45°	3039
50°	1944
55°	1567
60°	1360
65°	1245
70°	1026
75°	1017
80°	758
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3039 cd/sqm

TEST NUMBER: P1288656

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLP1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.2	14.4
10°-20°	37.6	29.9
20°-30°	34.1	27.0
30°-40°	20.5	16.2
40°-50°	8.1	6.5
50°-60°	3.7	3.0
60°-70°	2.3	1.8
70°-80°	1.2	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	89.9	71.3
0°-40°	110.3	87.5
0°-60°	122.2	96.9
0°-90°	126.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	126.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	209	
5°	199	18
15°	136	38
25°	74	34
35°	32	20
45°	10	8
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1288656

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLP1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	208.6
1°	208.6
2°	207.6
3°	205.5
4°	202.7
5°	199.4
6°	195.1
7°	190.1
8°	184.5
9°	178.8
10°	172.7
11°	165.6
12°	158.3
13°	151.1
14°	143.8
15°	136.1
17.5°	118.1
20°	101.8
22.5°	87.0
25°	74.3
27.5°	62.3
30°	51.3
32.5°	41.3
35°	32.2
37.5°	24.6
40°	18.3
42.5°	13.4
45°	9.8
47.5°	7.5
50°	5.7
52.5°	4.7
55°	4.1
57.5°	3.5
60°	3.1
62.5°	2.6
65°	2.4
67.5°	2.0
70°	1.6
72.5°	1.4
75°	1.2
77.5°	1.0
80°	0.6
82.5°	0.4
85°	0.4
87.5°	0.2



TEST NUMBER: P1288656

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLP1GPH_4000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)