

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288705

Luminaire Tested: P3AS05R25W2N902765DE010 E3PHLP1MW\_5000K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1288705  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R25W2N902765DE010 E3PHLP1MW\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,  
E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 230.0 lumens  
Efficiency: N/A  
Efficacy: 39.0 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1288705

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3PHLP1MW\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1288705

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3PHLP1MW\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 102 | 100 | 97  |  | 98  | 96  | 95  |  | 95  | 93  | 92  | 90  |
| 2   | 105 | 99  | 94  | 90  | 103 | 97  | 93  | 89  | 94  | 90  | 87  |  | 91  | 88  | 85  |  | 88  | 85  | 83  | 81  |
| 3   | 99  | 91  | 85  | 80  | 97  | 90  | 84  | 80  | 87  | 82  | 78  |  | 84  | 80  | 77  |  | 82  | 79  | 76  | 74  |
| 4   | 93  | 84  | 78  | 73  | 91  | 83  | 77  | 73  | 81  | 76  | 72  |  | 79  | 74  | 71  |  | 77  | 73  | 70  | 68  |
| 5   | 88  | 79  | 72  | 67  | 86  | 78  | 71  | 67  | 76  | 70  | 66  |  | 74  | 69  | 66  |  | 72  | 68  | 65  | 63  |
| 6   | 84  | 74  | 67  | 62  | 82  | 73  | 66  | 62  | 71  | 66  | 61  |  | 70  | 65  | 61  |  | 68  | 64  | 61  | 59  |
| 7   | 79  | 69  | 63  | 58  | 78  | 68  | 62  | 58  | 67  | 61  | 57  |  | 66  | 61  | 57  |  | 65  | 60  | 57  | 55  |
| 8   | 76  | 65  | 59  | 54  | 74  | 65  | 58  | 54  | 63  | 58  | 54  |  | 62  | 57  | 54  |  | 61  | 57  | 53  | 52  |
| 9   | 72  | 62  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 55  | 51  |  | 59  | 54  | 51  |  | 58  | 54  | 50  | 49  |
| 10  | 69  | 59  | 52  | 48  | 68  | 58  | 52  | 48  | 57  | 52  | 48  |  | 56  | 51  | 48  |  | 56  | 51  | 48  | 46  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 77275 |
| 5°  | 73013 |
| 10° | 62056 |
| 15° | 49149 |
| 20° | 37360 |
| 25° | 27873 |
| 30° | 20256 |
| 35° | 14348 |
| 40° | 9733  |
| 45° | 6791  |
| 50° | 5697  |
| 55° | 5505  |
| 60° | 5789  |
| 65° | 5967  |
| 70° | 5898  |
| 75° | 6354  |
| 80° | 7324  |
| 85° | 7296  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 82.5°  
Luminance: 7728 cd/sqm

TEST NUMBER: P1288705

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3PHLP1MW\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 29.9   | 13.0      |
| 10°-20°   | 59.9   | 26.1      |
| 20°-30°   | 53.1   | 23.1      |
| 30°-40°   | 33.8   | 14.7      |
| 40°-50°   | 17.9   | 7.8       |
| 50°-60°   | 13.1   | 5.7       |
| 60°-70°   | 11.2   | 4.9       |
| 70°-80°   | 7.9    | 3.4       |
| 80°-90°   | 3.2    | 1.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 142.9  | 62.1      |
| 0°-40°    | 176.7  | 76.8      |
| 0°-60°    | 207.7  | 90.3      |
| 0°-90°    | 230.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 230.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 352 |      |
| 5°  | 332 | 30   |
| 15° | 216 | 60   |
| 25° | 115 | 53   |
| 35° | 54  | 34   |
| 45° | 22  | 18   |
| 55° | 14  | 13   |
| 65° | 12  | 11   |
| 75° | 8   | 8    |
| 85° | 3   | 3    |
| 90° | 0   |      |

TEST NUMBER: P1288705

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3PHLP1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 352.4 |
| 2.5°  | 347.2 |
| 5°    | 331.7 |
| 7.5°  | 307.5 |
| 10°   | 278.7 |
| 12.5° | 247.6 |
| 15°   | 216.5 |
| 17.5° | 186.6 |
| 20°   | 160.1 |
| 22.5° | 135.9 |
| 25°   | 115.2 |
| 27.5° | 96.7  |
| 30°   | 80.0  |
| 32.5° | 65.6  |
| 35°   | 53.6  |
| 37.5° | 42.6  |
| 40°   | 34.0  |
| 42.5° | 27.1  |
| 45°   | 21.9  |
| 47.5° | 19.0  |
| 50°   | 16.7  |
| 52.5° | 15.5  |
| 55°   | 14.4  |
| 57.5° | 13.8  |
| 60°   | 13.2  |
| 62.5° | 12.1  |
| 65°   | 11.5  |
| 67.5° | 10.4  |
| 70°   | 9.2   |
| 72.5° | 8.6   |
| 75°   | 7.5   |
| 77.5° | 6.3   |
| 80°   | 5.8   |
| 82.5° | 4.6   |
| 85°   | 2.9   |
| 87.5° | 1.2   |
| 90°   | 0.0   |

(END OF REPORT)