

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288843

Luminaire Tested: P3AS05R30W2N902750DE010 E3DLP1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288843
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R30W2N902750DE010 E3DLP1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 419.1 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288843

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DLP1WH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288843

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DLP1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	89	88
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	85	84
4	101	95	90	86	99	94	89	86	92	88	85	90	87	84	88	85	83	82	81	80
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	77	76
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	74	73
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71	70	69
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	68	67
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	65	64
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	244498
5°	232709
10°	195743
15°	141159
20°	87554
25°	49793
30°	27650
35°	15044
40°	7929
45°	4311
50°	2286
55°	1529
60°	1403
65°	1453
70°	1282
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4311 cd/sqm

TEST NUMBER: P1288843

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DLP1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	22.7
10°-20°	169.2	40.4
20°-30°	97.8	23.3
30°-40°	37.1	8.9
40°-50°	11.4	2.7
50°-60°	3.8	0.9
60°-70°	2.6	0.6
70°-80°	1.4	0.3
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	362.2	86.4
0°-40°	399.3	95.3
0°-60°	414.6	98.9
0°-90°	419.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	419.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1115	
5°	1057	95
15°	622	169
25°	206	98
35°	56	37
45°	14	11
55°	4	4
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1288843

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DLP1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1115.0
1°	1114.2
2°	1107.5
3°	1094.8
4°	1079.0
5°	1057.2
6°	1029.5
7°	998.6
8°	964.2
9°	923.0
10°	879.1
11°	831.6
12°	781.3
13°	728.7
14°	675.3
15°	621.8
17.5°	490.4
20°	375.2
22.5°	278.3
25°	205.8
27.5°	149.6
30°	109.2
32.5°	78.8
35°	56.2
37.5°	39.2
40°	27.7
42.5°	19.4
45°	13.9
47.5°	9.5
50°	6.7
52.5°	4.7
55°	4.0
57.5°	3.6
60°	3.2
62.5°	2.8
65°	2.8
67.5°	2.4
70°	2.0
72.5°	1.6
75°	1.2
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.0



TEST NUMBER: P1288843

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DLP1WH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)