

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291321

Luminaire Tested: P3AS05R70W2N902750DE010 E3DL1WMH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1291321  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R70W2N902750DE010 E3DL1WMH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 5000K CCT AND, 90CRI ,  
E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 402.0 lumens  
Efficiency: N/A  
Efficacy: 68.1 lumens/watt  
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1291321  
CATALOG NUMBER: P3AS05R70W2N902750DE010 E3DL1WMH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1291321  
 CATALOG NUMBER: P3AS05R70W2N902750DE010 E3DL1WMH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	77823
5°	76887
10°	74659
15°	71510
20°	66972
25°	60850
30°	52565
35°	41894
40°	30514
45°	20064
50°	9381
55°	2906
60°	2807
65°	2698
70°	2565
75°	2711
80°	2526
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 20064 cd/sqm



TEST NUMBER: P1291321

CATALOG NUMBER: P3AS05R70W2N902750DE010 E3DL1WMH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	32.9	8.2
10°-20°	88.2	21.9
20°-30°	114.6	28.5
30°-40°	97.2	24.2
40°-50°	50.1	12.5
50°-60°	9.7	2.4
60°-70°	5.2	1.3
70°-80°	3.2	0.8
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	235.6	58.6
0°-40°	332.8	82.8
0°-60°	392.6	97.7
0°-90°	402.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	402.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	355	
5°	349	33
15°	315	88
25°	252	115
35°	156	97
45°	65	50
55°	8	10
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1291321  
CATALOG NUMBER: P3AS05R70W2N902750DE010 E3DL1WMH\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	354.9
2.5°	353.7
5°	349.3
7.5°	342.9
10°	335.3
12.5°	325.8
15°	315.0
17.5°	301.8
20°	287.0
22.5°	270.3
25°	251.5
27.5°	230.3
30°	207.6
32.5°	182.4
35°	156.5
37.5°	130.9
40°	106.6
42.5°	83.8
45°	64.7
47.5°	47.5
50°	27.5
52.5°	12.0
55°	7.6
57.5°	7.2
60°	6.4
62.5°	6.0
65°	5.2
67.5°	4.8
70°	4.0
72.5°	3.6
75°	3.2
77.5°	2.4
80°	2.0
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)