

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288860

Luminaire Tested: P3AS05R30W2N902750DE010 E3PHLD1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288860
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R30W2N902750DE010 E3PHLD1MW_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 4000K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 312.0 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288860

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3PHLD1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288860

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3PHLD1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				0				0
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90											90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80											80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	71											71
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65											65
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59											59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54											54
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50											50
8	72	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	48	46											46
9	68	57	50	45	66	56	49	45	55	49	45	54	49	45	53	48	44	43											43
10	64	53	47	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40											40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76880
5°	73475
10°	63392
15°	52532
20°	43077
25°	34720
30°	27979
35°	22914
40°	19036
45°	16157
50°	13816
55°	11928
60°	10657
65°	9288
70°	8142
75°	6863
80°	5051
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16157 cd/sqm

TEST NUMBER: P1288860

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3PHLD1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.3	9.7
10°-20°	64.5	20.7
20°-30°	66.2	21.2
30°-40°	54.1	17.3
40°-50°	40.4	13.0
50°-60°	28.4	9.1
60°-70°	17.8	5.7
70°-80°	8.6	2.8
80°-90°	1.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	160.9	51.6
0°-40°	215.0	68.9
0°-60°	283.9	91.0
0°-90°	312.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	312.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	351	
5°	334	30
15°	231	65
25°	144	66
35°	86	54
45°	52	40
55°	31	28
65°	18	18
75°	8	9
85°	1	2
90°	0	

TEST NUMBER: P1288860

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3PHLD1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	350.6
2.5°	347.1
5°	333.8
7.5°	311.8
10°	284.7
12.5°	258.0
15°	231.4
17.5°	207.1
20°	184.6
22.5°	163.2
25°	143.5
27.5°	126.1
30°	110.5
32.5°	97.8
35°	85.6
37.5°	75.8
40°	66.5
42.5°	59.0
45°	52.1
47.5°	45.7
50°	40.5
52.5°	35.9
55°	31.2
57.5°	27.8
60°	24.3
62.5°	20.8
65°	17.9
67.5°	15.0
70°	12.7
72.5°	10.4
75°	8.1
77.5°	5.8
80°	4.0
82.5°	2.3
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)