

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291385

Luminaire Tested: P3AS05R70W2N902765DE010 E3CD1MB_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R70W2N902765DE010 E3CD1MB_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 6500K CCT AND, 90CRI ,
E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 499.0 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291385
CATALOG NUMBER: P3AS05R70W2N902765DE010 E3CD1MB_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1291385

CATALOG NUMBER: P3AS05R70W2N902765DE010 E3CD1MB_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78			
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53			
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99093
5°	94541
10°	89956
15°	87560
20°	84311
25°	79795
30°	74214
35°	62346
40°	40190
45°	18669
50°	4912
55°	1223
60°	1228
65°	1038
70°	1026
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18669 cd/sqm



TEST NUMBER: P1291385

CATALOG NUMBER: P3AS05R70W2N902765DE010 E3CD1MB_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.2	8.1
10°-20°	108.4	21.7
20°-30°	151.4	30.3
30°-40°	140.4	28.1
40°-50°	50.3	10.1
50°-60°	4.3	0.9
60°-70°	2.1	0.4
70°-80°	1.4	0.3
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	300.0	60.1
0°-40°	440.3	88.2
0°-60°	495.0	99.2
0°-90°	499.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	499.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	452	
5°	430	40
15°	386	108
25°	330	151
35°	233	140
45°	60	50
55°	3	4
65°	2	2
75°	1	1
85°	0	1
90°	0	



TEST NUMBER: P1291385

CATALOG NUMBER: P3AS05R70W2N902765DE010 E3CD1MB_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	451.9
2.5°	445.1
5°	429.5
7.5°	415.2
10°	404.0
12.5°	394.8
15°	385.7
17.5°	374.5
20°	361.3
22.5°	346.2
25°	329.8
27.5°	313.1
30°	293.1
32.5°	267.6
35°	232.9
37.5°	188.6
40°	140.4
42.5°	95.7
45°	60.2
47.5°	33.5
50°	14.4
52.5°	4.8
55°	3.2
57.5°	2.8
60°	2.8
62.5°	2.4
65°	2.0
67.5°	2.0
70°	1.6
72.5°	1.6
75°	1.2
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)