

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291408

Luminaire Tested: P3AS05R70W2N902765DE010 E3D1LI_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291408
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R70W2N902765DE010 E3D1LI_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 5000K CCT AND, 90CRI ,
E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 476.0 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291408
CATALOG NUMBER: P3AS05R70W2N902765DE010 E3D1LI_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1291408

CATALOG NUMBER: P3AS05R70W2N902765DE010 E3D1LI_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			79
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			57
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92558
5°	87277
10°	82742
15°	81272
20°	78337
25°	73843
30°	73302
35°	63845
40°	41306
45°	19537
50°	2729
55°	229
60°	175
65°	208
70°	128
75°	169
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19537 cd/sqm



TEST NUMBER: P1291408

CATALOG NUMBER: P3AS05R70W2N902765DE010 E3D1LI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.0	7.8
10°-20°	100.5	21.1
20°-30°	142.2	29.9
30°-40°	142.9	30.0
40°-50°	51.4	10.8
50°-60°	1.4	0.3
60°-70°	0.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	279.8	58.8
0°-40°	422.7	88.8
0°-60°	475.5	99.9
0°-90°	476.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	476.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	422	
5°	396	37
15°	358	101
25°	305	142
35°	238	143
45°	63	51
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1291408

CATALOG NUMBER: P3AS05R70W2N902765DE010 E3D1LI_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	422.1
1°	420.9
2°	417.2
3°	411.3
4°	403.9
5°	396.5
6°	389.4
7°	384.0
8°	379.1
9°	375.2
10°	371.6
11°	368.7
12°	366.0
13°	363.2
14°	360.7
15°	358.0
16°	354.6
17°	351.1
18°	346.8
19°	341.5
20°	335.7
21°	329.2
22°	322.8
23°	316.5
24°	310.5
25°	305.2
26°	301.5
27°	298.5
28°	296.2
29°	293.4
30°	289.5
31°	283.9
32°	275.9
32.5°	271.4
33°	265.3
34°	253.4
35°	238.5
36°	222.1
37°	203.5
37.5°	194.9
38°	183.2
39°	162.3
40°	144.3
42.5°	99.9
45°	63.0



TEST NUMBER: P1291408
CATALOG NUMBER: P3AS05R70W2N902765DE010 E3D1LI_5000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	33.8
50°	8.0
52.5°	1.0
55°	0.6
57.5°	0.6
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)