

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291414

Luminaire Tested: P3AS05R70W2N902765DE010 E3D1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R70W2N902765DE010 E3D1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 5000K CCT AND, 90CRI ,
E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 499.0 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291414
CATALOG NUMBER: P3AS05R70W2N902765DE010 E3D1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1291414

CATALOG NUMBER: P3AS05R70W2N902765DE010 E3D1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.2	8.1
10°-20°	108.4	21.7
20°-30°	151.4	30.3
30°-40°	140.4	28.1
40°-50°	50.3	10.1
50°-60°	4.3	0.9
60°-70°	2.1	0.4
70°-80°	1.4	0.3
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	300.0	60.1
0°-40°	440.3	88.2
0°-60°	495.0	99.2
0°-90°	499.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	499.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	452	
5°	430	40
15°	386	108
25°	330	151
35°	233	140
45°	60	50
55°	3	4
65°	2	2
75°	1	1
85°	0	1
90°	0	



TEST NUMBER: P1291414
CATALOG NUMBER: P3AS05R70W2N902765DE010 E3D1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	451.9
2.5°	445.1
5°	429.5
7.5°	415.2
10°	404.0
12.5°	394.8
15°	385.7
17.5°	374.5
20°	361.3
22.5°	346.2
25°	329.8
27.5°	313.1
30°	293.1
32.5°	267.6
35°	232.9
37.5°	188.6
40°	140.4
42.5°	95.7
45°	60.2
47.5°	33.5
50°	14.4
52.5°	4.8
55°	3.2
57.5°	2.8
60°	2.8
62.5°	2.4
65°	2.0
67.5°	2.0
70°	1.6
72.5°	1.6
75°	1.2
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)