

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288974

Luminaire Tested: P3AS05R30W2N902765DE010 E3DLD1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288974
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R30W2N902765DE010 E3DLD1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 6500K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 159.0 lumens
Efficiency: N/A
Efficacy: 27.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288974

CATALOG NUMBER: P3AS05R30W2N902765DE010 E3DLD1GPH_6500K

Luminous Intensity Polar Plot



TEST NUMBER: P1288974

CATALOG NUMBER: P3AS05R30W2N902765DE010 E3DLD1GPH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76		
4	94	85	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70		
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59		
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55		
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48		
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37563
5°	36716
10°	34157
15°	30375
20°	26136
25°	22138
30°	18383
35°	14429
40°	10334
45°	6791
50°	3855
55°	2523
60°	2412
65°	2231
70°	1988
75°	1779
80°	1768
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6791 cd/sqm

TEST NUMBER: P1288974

CATALOG NUMBER: P3AS05R30W2N902765DE010 E3DLD1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.5	9.7
10°-20°	37.2	23.4
20°-30°	41.9	26.4
30°-40°	33.5	21.1
40°-50°	17.2	10.8
50°-60°	6.5	4.1
60°-70°	4.3	2.7
70°-80°	2.3	1.4
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	94.6	59.5
0°-40°	128.1	80.6
0°-60°	151.8	95.5
0°-90°	159.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	159.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	171	
5°	167	15
15°	134	37
25°	92	42
35°	54	33
45°	22	17
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1288974

CATALOG NUMBER: P3AS05R30W2N902765DE010 E3DLD1GPH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	171.3
1°	171.3
2°	170.7
3°	169.7
4°	168.4
5°	166.8
6°	164.9
7°	162.3
8°	159.6
9°	156.5
10°	153.4
11°	149.8
12°	146.1
13°	142.2
14°	138.1
15°	133.8
17.5°	122.9
20°	112.0
22.5°	101.5
25°	91.5
27.5°	81.8
30°	72.6
32.5°	63.2
35°	53.9
37.5°	44.7
40°	36.1
42.5°	28.5
45°	21.9
47.5°	16.2
50°	11.3
52.5°	8.0
55°	6.6
57.5°	6.0
60°	5.5
62.5°	4.9
65°	4.3
67.5°	3.7
70°	3.1
72.5°	2.5
75°	2.1
77.5°	1.8
80°	1.4
82.5°	1.0
85°	0.6
87.5°	0.2



TEST NUMBER: P1288974

CATALOG NUMBER: P3AS05R30W2N902765DE010 E3DLD1GPH_6500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)