

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289157

Luminaire Tested: P3AS05R35W2N902750DE010 E3DLP1GPH\_4000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1289157  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R35W2N902750DE010 E3DLP1GPH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 4000K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 128.0 lumens  
Efficiency: N/A  
Efficacy: 21.7 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1289157

CATALOG NUMBER: P3AS05R35W2N902750DE010 E3DLP1GPH\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1289157

CATALOG NUMBER: P3AS05R35W2N902750DE010 E3DLP1GPH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 97  | 93  | 97  | 94  | 91  |  | 94  | 92  | 89  |  | 91  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 85  | 91  | 87  | 84  |  | 89  | 85  | 82  |  | 86  |
| 4   | 97  | 89  | 83  | 79  | 95  | 88  | 82  | 78  | 86  | 81  | 77  |  | 83  | 80  | 76  |  | 82  |
| 5   | 92  | 83  | 77  | 73  | 90  | 82  | 77  | 73  | 80  | 76  | 72  |  | 79  | 75  | 71  |  | 77  |
| 6   | 87  | 78  | 72  | 68  | 86  | 77  | 72  | 68  | 76  | 71  | 67  |  | 75  | 70  | 67  |  | 73  |
| 7   | 83  | 74  | 68  | 63  | 82  | 73  | 67  | 63  | 72  | 67  | 63  |  | 71  | 66  | 63  |  | 69  |
| 8   | 79  | 70  | 64  | 60  | 78  | 69  | 63  | 59  | 68  | 63  | 59  |  | 67  | 62  | 59  |  | 66  |
| 9   | 76  | 66  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 59  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 61  | 56  | 53  |  | 61  | 56  | 53  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 41137 |
| 5°  | 40128 |
| 10° | 36695 |
| 15° | 31147 |
| 20° | 24642 |
| 25° | 18654 |
| 30° | 13572 |
| 35° | 9182  |
| 40° | 5639  |
| 45° | 3225  |
| 50° | 1944  |
| 55° | 1567  |
| 60° | 1403  |
| 65° | 1245  |
| 70° | 1026  |
| 75° | 1017  |
| 80° | 1010  |
| 85° | 1006  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3225 cd/sqm

TEST NUMBER: P1289157

CATALOG NUMBER: P3AS05R35W2N902750DE010 E3DLP1GPH\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 16.8   | 13.2      |
| 10°-20°   | 37.8   | 29.5      |
| 20°-30°   | 35.4   | 27.6      |
| 30°-40°   | 21.7   | 16.9      |
| 40°-50°   | 8.5    | 6.7       |
| 50°-60°   | 3.7    | 2.9       |
| 60°-70°   | 2.4    | 1.9       |
| 70°-80°   | 1.3    | 1.0       |
| 80°-90°   | 0.4    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 90.0   | 70.3      |
| 0°-40°    | 111.7  | 87.2      |
| 0°-60°    | 124.0  | 96.8      |
| 0°-90°    | 128.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 128.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 188 |      |
| 5°  | 182 | 17   |
| 15° | 137 | 38   |
| 25° | 77  | 35   |
| 35° | 34  | 22   |
| 45° | 10  | 9    |
| 55° | 4   | 4    |
| 65° | 2   | 2    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1289157

CATALOG NUMBER: P3AS05R35W2N902750DE010 E3DLP1GPH\_4000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 187.6 |
| 1°    | 187.8 |
| 2°    | 187.2 |
| 3°    | 186.0 |
| 4°    | 184.3 |
| 5°    | 182.3 |
| 6°    | 179.7 |
| 7°    | 176.8 |
| 8°    | 173.2 |
| 9°    | 169.3 |
| 10°   | 164.8 |
| 11°   | 160.0 |
| 12°   | 154.9 |
| 13°   | 149.4 |
| 14°   | 143.3 |
| 15°   | 137.2 |
| 17.5° | 121.4 |
| 20°   | 105.6 |
| 22.5° | 90.5  |
| 25°   | 77.1  |
| 27.5° | 64.6  |
| 30°   | 53.6  |
| 32.5° | 43.4  |
| 35°   | 34.3  |
| 37.5° | 26.2  |
| 40°   | 19.7  |
| 42.5° | 14.2  |
| 45°   | 10.4  |
| 47.5° | 7.5   |
| 50°   | 5.7   |
| 52.5° | 4.7   |
| 55°   | 4.1   |
| 57.5° | 3.5   |
| 60°   | 3.2   |
| 62.5° | 2.8   |
| 65°   | 2.4   |
| 67.5° | 2.0   |
| 70°   | 1.6   |
| 72.5° | 1.4   |
| 75°   | 1.2   |
| 77.5° | 1.0   |
| 80°   | 0.8   |
| 82.5° | 0.6   |
| 85°   | 0.4   |
| 87.5° | 0.2   |



TEST NUMBER: P1289157

CATALOG NUMBER: P3AS05R35W2N902750DE010 E3DLP1GPH\_4000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)