

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291556

Luminaire Tested: P3AS09R15W2N902750DE010 E3D1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291556
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R15W2N902750DE010 E3D1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 5000K CCT AND, 90CRI ,
E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 744.1 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291556
CATALOG NUMBER: P3AS09R15W2N902750DE010 E3D1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1291556

CATALOG NUMBER: P3AS09R15W2N902750DE010 E3D1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 106 | 104 | 103 | 103 | 101 | 100 | 100 | 98 | 98 | 98 | 98 |
| 2 | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 104 | 105 | 103 | 101 | 102 | 101 | 99 | 99 | 98 | 97 | 96 | 96 | 96 | 96 |
| 3 | 110 | 106 | 103 | 100 | 108 | 105 | 102 | 100 | 102 | 100 | 98 | 100 | 98 | 97 | 98 | 97 | 95 | 94 | 94 | 94 | 94 |
| 4 | 107 | 103 | 100 | 97 | 106 | 102 | 99 | 97 | 100 | 97 | 95 | 98 | 96 | 94 | 97 | 95 | 93 | 92 | 92 | 92 | 92 |
| 5 | 105 | 100 | 97 | 94 | 104 | 99 | 96 | 94 | 98 | 95 | 93 | 96 | 94 | 92 | 95 | 93 | 92 | 91 | 91 | 91 | 91 |
| 6 | 103 | 98 | 94 | 92 | 102 | 97 | 94 | 92 | 96 | 93 | 91 | 95 | 92 | 91 | 94 | 92 | 90 | 89 | 89 | 89 | 89 |
| 7 | 101 | 96 | 92 | 90 | 100 | 95 | 92 | 90 | 94 | 91 | 89 | 93 | 91 | 89 | 92 | 90 | 89 | 88 | 88 | 88 | 88 |
| 8 | 99 | 94 | 90 | 88 | 98 | 93 | 90 | 88 | 92 | 90 | 88 | 92 | 89 | 87 | 91 | 89 | 87 | 86 | 86 | 86 | 86 |
| 9 | 97 | 92 | 89 | 87 | 97 | 92 | 89 | 86 | 91 | 88 | 86 | 90 | 88 | 86 | 90 | 87 | 86 | 85 | 85 | 85 | 85 |
| 10 | 96 | 90 | 87 | 85 | 95 | 90 | 87 | 85 | 89 | 87 | 85 | 89 | 86 | 85 | 88 | 86 | 85 | 84 | 84 | 84 | 84 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1446156 |
| 5° | 1212015 |
| 10° | 570909 |
| 15° | 172124 |
| 20° | 63682 |
| 25° | 24751 |
| 30° | 9242 |
| 35° | 2838 |
| 40° | 1002 |
| 45° | 558 |
| 50° | 409 |
| 55° | 459 |
| 60° | 526 |
| 65° | 311 |
| 70° | 385 |
| 75° | 508 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 558 cd/sqm



TEST NUMBER: P1291556

CATALOG NUMBER: P3AS09R15W2N902750DE010 E3D1MW_5000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 425.7 | 57.2 |
| 10°-20° | 253.0 | 34.0 |
| 20°-30° | 53.2 | 7.1 |
| 30°-40° | 8.6 | 1.2 |
| 40°-50° | 1.5 | 0.2 |
| 50°-60° | 1.1 | 0.1 |
| 60°-70° | 0.7 | 0.1 |
| 70°-80° | 0.4 | 0.1 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 731.9 | 98.4 |
| 0°-40° | 740.5 | 99.5 |
| 0°-60° | 743.0 | 99.9 |
| 0°-90° | 744.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 744.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 6595 | |
| 5° | 5506 | 426 |
| 15° | 758 | 253 |
| 25° | 102 | 53 |
| 35° | 11 | 9 |
| 45° | 2 | 1 |
| 55° | 1 | 1 |
| 65° | 1 | 1 |
| 75° | 1 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1291556
CATALOG NUMBER: P3AS09R15W2N902750DE010 E3D1MW_5000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 6595.0 |
| 1° | 6574.4 |
| 2° | 6469.7 |
| 3° | 6260.3 |
| 4° | 5953.3 |
| 5° | 5506.2 |
| 6° | 4981.0 |
| 7° | 4380.4 |
| 8° | 3806.9 |
| 9° | 3157.5 |
| 10° | 2564.0 |
| 12.5° | 1383.5 |
| 15° | 758.2 |
| 17.5° | 444.1 |
| 20° | 272.9 |
| 22.5° | 167.1 |
| 25° | 102.3 |
| 27.5° | 61.8 |
| 30° | 36.5 |
| 32.5° | 20.6 |
| 35° | 10.6 |
| 37.5° | 5.9 |
| 40° | 3.5 |
| 42.5° | 2.4 |
| 45° | 1.8 |
| 47.5° | 1.2 |
| 50° | 1.2 |
| 52.5° | 1.2 |
| 55° | 1.2 |
| 57.5° | 1.2 |
| 60° | 1.2 |
| 62.5° | 0.6 |
| 65° | 0.6 |
| 67.5° | 0.6 |
| 70° | 0.6 |
| 72.5° | 0.6 |
| 75° | 0.6 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)