

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291595

Luminaire Tested: P3AS09R15W2N902750DE010 E3DL1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291595
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R15W2N902750DE010 E3DL1WMH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 614.0 lumens
Efficiency: N/A
Efficacy: 68.2 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291595
CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DL1WMH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1291595
 CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DL1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97		95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93		91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88		87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85		83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81		80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78		77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75		74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73		72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70		69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	524519
5°	465594
10°	323330
15°	191216
20°	108906
25°	62254
30°	34436
35°	18364
40°	10162
45°	5489
50°	3446
55°	2714
60°	2324
65°	2127
70°	1923
75°	2033
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5489 cd/sqm



TEST NUMBER: P1291595

CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DL1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.9	29.3
10°-20°	237.4	38.7
20°-30°	122.2	19.9
30°-40°	45.9	7.5
40°-50°	15.0	2.4
50°-60°	6.5	1.1
60°-70°	4.1	0.7
70°-80°	2.5	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	539.5	87.9
0°-40°	585.4	95.3
0°-60°	606.8	98.8
0°-90°	614.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	614.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2392	
5°	2115	180
15°	842	237
25°	257	122
35°	69	46
45°	18	15
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1291595
CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DL1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2392.0
1°	2387.3
2°	2355.9
3°	2296.2
4°	2217.5
5°	2115.2
6°	1999.2
7°	1872.1
8°	1730.7
9°	1591.1
10°	1452.1
12.5°	1117.3
15°	842.3
17.5°	630.5
20°	466.7
22.5°	348.4
25°	257.3
27.5°	187.5
30°	136.0
32.5°	96.4
35°	68.6
37.5°	49.1
40°	35.5
42.5°	25.4
45°	17.7
47.5°	13.0
50°	10.1
52.5°	8.3
55°	7.1
57.5°	5.9
60°	5.3
62.5°	4.7
65°	4.1
67.5°	3.5
70°	3.0
72.5°	3.0
75°	2.4
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)