

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291627

Luminaire Tested: P3AS09R15W2N902750DE010 E3DLP1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291627
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R15W2N902750DE010 E3DLP1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 160.0 lumens
Efficiency: N/A
Efficacy: 17.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291627
CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DLP1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1291627
 CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DLP1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 113 | 110 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 95 | 93 | 93 | 93 | 93 |
| 2 | 108 | 103 | 98 | 95 | 105 | 101 | 97 | 94 | 98 | 95 | 92 | 95 | 92 | 90 | 92 | 90 | 88 | 86 | 86 | 86 | 86 |
| 3 | 102 | 96 | 91 | 87 | 100 | 94 | 90 | 86 | 92 | 88 | 85 | 89 | 86 | 83 | 87 | 84 | 82 | 80 | 80 | 80 | 80 |
| 4 | 97 | 90 | 84 | 80 | 95 | 88 | 83 | 79 | 86 | 82 | 78 | 84 | 81 | 78 | 82 | 79 | 77 | 75 | 75 | 75 | 75 |
| 5 | 93 | 84 | 78 | 74 | 91 | 83 | 78 | 74 | 81 | 77 | 73 | 80 | 76 | 72 | 78 | 75 | 72 | 70 | 70 | 70 | 70 |
| 6 | 88 | 79 | 73 | 69 | 87 | 79 | 73 | 69 | 77 | 72 | 69 | 76 | 71 | 68 | 74 | 71 | 68 | 66 | 66 | 66 | 66 |
| 7 | 84 | 75 | 69 | 65 | 83 | 74 | 69 | 65 | 73 | 68 | 64 | 72 | 67 | 64 | 71 | 67 | 64 | 62 | 62 | 62 | 62 |
| 8 | 80 | 71 | 65 | 61 | 79 | 71 | 65 | 61 | 69 | 64 | 61 | 68 | 64 | 61 | 67 | 63 | 60 | 59 | 59 | 59 | 59 |
| 9 | 77 | 68 | 62 | 58 | 76 | 67 | 62 | 58 | 66 | 61 | 58 | 65 | 61 | 57 | 64 | 60 | 57 | 56 | 56 | 56 | 56 |
| 10 | 74 | 64 | 59 | 55 | 73 | 64 | 59 | 55 | 63 | 58 | 55 | 62 | 58 | 55 | 62 | 57 | 54 | 53 | 53 | 53 | 53 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 68986 |
| 5° | 63768 |
| 10° | 50901 |
| 15° | 38457 |
| 20° | 29286 |
| 25° | 22308 |
| 30° | 15977 |
| 35° | 10440 |
| 40° | 6383 |
| 45° | 3876 |
| 50° | 2559 |
| 55° | 1988 |
| 60° | 1710 |
| 65° | 1505 |
| 70° | 1346 |
| 75° | 1356 |
| 80° | 1010 |
| 85° | 755 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3876 cd/sqm



TEST NUMBER: P1291627

CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DLP1GPH_2700K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 25.7 | 16.0 |
| 10°-20° | 47.3 | 29.6 |
| 20°-30° | 42.1 | 26.3 |
| 30°-40° | 24.9 | 15.6 |
| 40°-50° | 10.2 | 6.4 |
| 50°-60° | 4.8 | 3.0 |
| 60°-70° | 2.9 | 1.8 |
| 70°-80° | 1.5 | 1.0 |
| 80°-90° | 0.4 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 115.2 | 72.0 |
| 0°-40° | 140.1 | 87.6 |
| 0°-60° | 155.1 | 96.9 |
| 0°-90° | 160.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 160.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 315 | |
| 5° | 290 | 26 |
| 15° | 169 | 47 |
| 25° | 92 | 42 |
| 35° | 39 | 25 |
| 45° | 12 | 10 |
| 55° | 5 | 5 |
| 65° | 3 | 3 |
| 75° | 2 | 2 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1291627
CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 314.6 |
| 1° | 313.9 |
| 2° | 311.5 |
| 3° | 306.9 |
| 4° | 299.1 |
| 5° | 289.7 |
| 6° | 279.6 |
| 7° | 267.6 |
| 8° | 255.1 |
| 9° | 242.4 |
| 10° | 228.6 |
| 12.5° | 197.2 |
| 15° | 169.4 |
| 17.5° | 145.5 |
| 20° | 125.5 |
| 22.5° | 107.8 |
| 25° | 92.2 |
| 27.5° | 77.2 |
| 30° | 63.1 |
| 32.5° | 50.4 |
| 35° | 39.0 |
| 37.5° | 29.9 |
| 40° | 22.3 |
| 42.5° | 16.6 |
| 45° | 12.5 |
| 47.5° | 9.6 |
| 50° | 7.5 |
| 52.5° | 6.2 |
| 55° | 5.2 |
| 57.5° | 4.4 |
| 60° | 3.9 |
| 62.5° | 3.4 |
| 65° | 2.9 |
| 67.5° | 2.6 |
| 70° | 2.1 |
| 72.5° | 1.8 |
| 75° | 1.6 |
| 77.5° | 1.0 |
| 80° | 0.8 |
| 82.5° | 0.5 |
| 85° | 0.3 |
| 87.5° | 0.3 |
| 90° | 0.0 |

(END OF REPORT)