

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289282

Luminaire Tested: P3AS05R35W2N902765DE010 E3DLD1GPH\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1289282  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R35W2N902765DE010 E3DLD1GPH\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 6500K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 158.0 lumens  
Efficiency: N/A  
Efficacy: 26.8 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1289282  
CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLD1GPH\_6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1289282

CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLD1GPH\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	44			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	36094
5°	35329
10°	33088
15°	29694
20°	25832
25°	22017
30°	18433
35°	14696
40°	10620
45°	6729
50°	3650
55°	2523
60°	2412
65°	2231
70°	2116
75°	1779
80°	1768
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6729 cd/sqm



TEST NUMBER: P1289282

CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLD1GPH\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	14.9	9.5
10°-20°	36.4	23.0
20°-30°	41.7	26.4
30°-40°	34.0	21.5
40°-50°	17.2	10.9
50°-60°	6.4	4.0
60°-70°	4.3	2.7
70°-80°	2.4	1.5
80°-90°	0.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	93.1	58.9
0°-40°	127.1	80.4
0°-60°	150.6	95.3
0°-90°	158.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	158.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	165	
5°	160	15
15°	131	36
25°	91	42
35°	55	34
45°	22	17
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1289282  
CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLD1GPH\_6500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	164.6
1°	164.4
2°	164.0
3°	163.2
4°	162.1
5°	160.5
6°	158.5
7°	156.6
8°	154.0
9°	151.5
10°	148.6
11°	145.5
12°	142.1
13°	138.4
14°	134.5
15°	130.8
17.5°	120.9
20°	110.7
22.5°	100.4
25°	91.0
27.5°	81.8
30°	72.8
32.5°	63.8
35°	54.9
37.5°	45.9
40°	37.1
42.5°	28.9
45°	21.7
47.5°	15.6
50°	10.7
52.5°	7.8
55°	6.6
57.5°	6.1
60°	5.5
62.5°	4.9
65°	4.3
67.5°	3.7
70°	3.3
72.5°	2.7
75°	2.1
77.5°	1.8
80°	1.4
82.5°	1.0
85°	0.6
87.5°	0.4



TEST NUMBER: P1289282  
CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLD1GPH\_6500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)