

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289294

Luminaire Tested: P3AS05R35W2N902765DE010 E3DLD1LI\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1289294  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R35W2N902765DE010 E3DLD1LI\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 6500K CCT AND, 90CRI ,  
E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 323.1 lumens  
Efficiency: N/A  
Efficacy: 54.8 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1289294  
CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLD1LI\_6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1289294

CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLD1LI\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	44			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	73788
5°	72221
10°	67623
15°	60704
20°	52808
25°	45003
30°	37702
35°	30035
40°	21698
45°	13738
50°	7505
55°	5199
60°	4912
65°	4566
70°	4360
75°	3728
80°	3536
85°	3019

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13738 cd/sqm



TEST NUMBER: P1289294

CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLD1LI\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	30.5	9.5
10°-20°	74.4	23.0
20°-30°	85.3	26.4
30°-40°	69.6	21.5
40°-50°	35.1	10.9
50°-60°	13.1	4.0
60°-70°	8.8	2.7
70°-80°	4.9	1.5
80°-90°	1.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	190.2	58.9
0°-40°	259.8	80.4
0°-60°	308.0	95.3
0°-90°	323.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	323.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	336	
5°	328	31
15°	267	74
25°	186	85
35°	112	70
45°	44	35
55°	14	13
65°	9	9
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1289294  
CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLD1LI\_6500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	336.5
1°	336.1
2°	335.3
3°	333.7
4°	331.3
5°	328.1
6°	324.1
7°	320.1
8°	314.9
9°	309.7
10°	303.7
11°	297.4
12°	290.6
13°	283.0
14°	275.0
15°	267.4
17.5°	247.1
20°	226.3
22.5°	205.2
25°	186.0
27.5°	167.2
30°	148.9
32.5°	130.5
35°	112.2
37.5°	93.8
40°	75.8
42.5°	59.1
45°	44.3
47.5°	31.9
50°	22.0
52.5°	16.0
55°	13.6
57.5°	12.4
60°	11.2
62.5°	10.0
65°	8.8
67.5°	7.6
70°	6.8
72.5°	5.6
75°	4.4
77.5°	3.6
80°	2.8
82.5°	2.0
85°	1.2
87.5°	0.8



TEST NUMBER: P1289294  
CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLD1LI\_6500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)