

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289313

Luminaire Tested: P3AS05R35W2N902765DE010 E3DLP1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289313
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R35W2N902765DE010 E3DLP1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 114.0 lumens
Efficiency: N/A
Efficacy: 19.3 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289313
CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLP1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1289313
 CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLP1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86		
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80		
4	97	89	83	79	95	88	82	78	86	81	77	83	80	76	82	78	76	74		
5	92	83	77	73	90	82	77	73	80	76	72	79	75	71	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65		
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61		
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57		
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54		
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36642
5°	35747
10°	32665
15°	27741
20°	21959
25°	16598
30°	12078
35°	8165
40°	5038
45°	2884
50°	1740
55°	1415
60°	1228
65°	1090
70°	898
75°	932
80°	884
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2884 cd/sqm



TEST NUMBER: P1289313

CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLP1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.0	13.2
10°-20°	33.7	29.5
20°-30°	31.5	27.6
30°-40°	19.3	16.9
40°-50°	7.6	6.7
50°-60°	3.4	2.9
60°-70°	2.1	1.8
70°-80°	1.1	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	80.2	70.3
0°-40°	99.5	87.2
0°-60°	110.4	96.8
0°-90°	114.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	114.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	167	
5°	162	15
15°	122	34
25°	69	32
35°	30	19
45°	9	8
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1289313
CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	167.1
1°	167.3
2°	166.8
3°	165.7
4°	164.1
5°	162.4
6°	160.1
7°	157.4
8°	154.3
9°	150.8
10°	146.7
11°	142.5
12°	138.0
13°	133.1
14°	127.6
15°	122.2
17.5°	108.1
20°	94.1
22.5°	80.6
25°	68.6
27.5°	57.6
30°	47.7
32.5°	38.6
35°	30.5
37.5°	23.3
40°	17.6
42.5°	12.6
45°	9.3
47.5°	6.7
50°	5.1
52.5°	4.2
55°	3.7
57.5°	3.2
60°	2.8
62.5°	2.5
65°	2.1
67.5°	1.8
70°	1.4
72.5°	1.2
75°	1.1
77.5°	0.9
80°	0.7
82.5°	0.5
85°	0.4
87.5°	0.2



TEST NUMBER: P1289313
CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)