

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291714

Luminaire Tested: P3AS09R15W2N902765DE010 E3D1LI_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291714
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R15W2N902765DE010 E3D1LI_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI ,
E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 683.1 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291714
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3D1LI_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1291714

CATALOG NUMBER: P3AS09R15W2N902765DE010 E3D1LI_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		100
1	116	114	112	111	113	112	110	109	108	107	105	104	103	102	101	100	99	98		98
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96		96
3	110	106	102	100	108	104	101	99	102	100	98	100	98	96	98	96	95	94		94
4	107	102	99	96	105	101	98	96	99	97	95	98	96	94	96	94	93	92		92
5	105	100	96	94	103	99	96	93	97	94	92	96	93	92	94	92	91	90		90
6	102	97	94	91	101	96	93	91	95	92	90	94	92	90	93	91	89	88		88
7	100	95	91	89	99	94	91	89	93	90	88	92	90	88	91	89	88	87		87
8	98	93	89	87	97	92	89	87	91	89	87	91	88	86	90	88	86	85		85
9	96	91	88	85	96	91	87	85	90	87	85	89	87	85	88	86	84	84		84
10	95	89	86	84	94	89	86	84	88	85	83	88	85	83	87	85	83	82		82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1300598
5°	1060552
10°	519407
15°	158979
20°	67323
25°	30461
30°	11875
35°	5488
40°	1718
45°	651
50°	273
55°	115
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 651 cd/sqm



TEST NUMBER: P1291714

CATALOG NUMBER: P3AS09R15W2N902765DE010 E3D1LI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	375.0	54.9
10°-20°	230.1	33.7
20°-30°	61.8	9.0
30°-40°	13.6	2.0
40°-50°	1.9	0.3
50°-60°	0.4	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	667.0	97.6
0°-40°	680.6	99.6
0°-60°	682.9	100.0
0°-90°	683.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	683.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5931	
5°	4818	375
15°	700	230
25°	126	62
35°	20	14
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1291714

CATALOG NUMBER: P3AS09R15W2N902765DE010 E3D1LI_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	5931.2
1°	5894.2
2°	5775.3
3°	5561.2
4°	5238.7
5°	4818.1
6°	4342.4
7°	3812.5
8°	3325.6
9°	2809.5
10°	2332.7
11°	1860.8
12°	1431.7
13°	1101.2
14°	871.7
15°	700.3
17.5°	434.1
20°	288.5
22.5°	194.2
25°	125.9
27.5°	74.6
30°	46.9
32.5°	31.6
35°	20.5
37.5°	11.4
40°	6.0
42.5°	3.4
45°	2.1
47.5°	1.3
50°	0.8
52.5°	0.5
55°	0.3
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1291714
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3D1LI_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)