

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289341

Luminaire Tested: P3AS05R35W2N902765DE010 E3DLP1WH\_5000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1289341  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R35W2N902765DE010 E3DLP1WH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 90CRI ,  
E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 419.0 lumens  
Efficiency: N/A  
Efficacy: 71.0 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1289341

CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLP1WH\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1289341

CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLP1WH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 | 102 | 100 | 99  | 98  | 97  | 96  | 96  | 96  | 95  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  | 97  | 95  | 93  | 94  | 93  | 91  | 91  | 91  | 90  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 92  | 89  | 93  | 90  | 88  | 91  | 88  | 86  | 86  | 86  | 85  |
| 4   | 100 | 94  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 84  | 89  | 85  | 83  | 87  | 84  | 82  | 82  | 82  | 80  |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 83  | 80  | 86  | 82  | 79  | 85  | 81  | 78  | 83  | 80  | 78  | 78  | 78  | 76  |
| 6   | 92  | 85  | 80  | 76  | 91  | 84  | 79  | 76  | 83  | 78  | 75  | 81  | 77  | 75  | 80  | 77  | 74  | 74  | 74  | 73  |
| 7   | 89  | 81  | 76  | 72  | 88  | 80  | 75  | 72  | 79  | 75  | 71  | 78  | 74  | 71  | 77  | 73  | 71  | 71  | 71  | 70  |
| 8   | 85  | 77  | 72  | 69  | 84  | 77  | 72  | 68  | 76  | 71  | 68  | 75  | 71  | 68  | 74  | 70  | 68  | 68  | 68  | 66  |
| 9   | 82  | 74  | 69  | 66  | 81  | 74  | 69  | 65  | 73  | 68  | 65  | 72  | 68  | 65  | 71  | 67  | 65  | 65  | 65  | 64  |
| 10  | 79  | 71  | 66  | 63  | 78  | 71  | 66  | 63  | 70  | 66  | 63  | 69  | 65  | 62  | 69  | 65  | 62  | 62  | 62  | 61  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 211321 |
| 5°  | 203103 |
| 10° | 176951 |
| 15° | 135529 |
| 20° | 90681  |
| 25° | 54874  |
| 30° | 31499  |
| 35° | 17614  |
| 40° | 9360   |
| 45° | 4807   |
| 50° | 2320   |
| 55° | 1835   |
| 60° | 1754   |
| 65° | 1453   |
| 70° | 1539   |
| 75° | 1356   |
| 80° | 1515   |
| 85° | 1006   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 4807 cd/sqm

TEST NUMBER: P1289341

CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLP1WH\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 83.9   | 20.0      |
| 10°-20°   | 162.7  | 38.8      |
| 20°-30°   | 106.5  | 25.4      |
| 30°-40°   | 43.2   | 10.3      |
| 40°-50°   | 13.0   | 3.1       |
| 50°-60°   | 4.4    | 1.1       |
| 60°-70°   | 3.0    | 0.7       |
| 70°-80°   | 1.7    | 0.4       |
| 80°-90°   | 0.6    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 353.1  | 84.3      |
| 0°-40°    | 396.4  | 94.6      |
| 0°-60°    | 413.7  | 98.7      |
| 0°-90°    | 419.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 419.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 964 |      |
| 5°  | 923 | 84   |
| 15° | 597 | 163  |
| 25° | 227 | 107  |
| 35° | 66  | 43   |
| 45° | 16  | 13   |
| 55° | 5   | 4    |
| 65° | 3   | 3    |
| 75° | 2   | 2    |
| 85° | 0   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1289341

CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLP1WH\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 963.7 |
| 1°    | 962.1 |
| 2°    | 957.7 |
| 3°    | 949.0 |
| 4°    | 938.6 |
| 5°    | 922.7 |
| 6°    | 902.7 |
| 7°    | 880.4 |
| 8°    | 855.3 |
| 9°    | 826.6 |
| 10°   | 794.7 |
| 11°   | 759.3 |
| 12°   | 722.2 |
| 13°   | 680.7 |
| 14°   | 641.3 |
| 15°   | 597.0 |
| 17.5° | 489.8 |
| 20°   | 388.6 |
| 22.5° | 298.9 |
| 25°   | 226.8 |
| 27.5° | 169.0 |
| 30°   | 124.4 |
| 32.5° | 91.3  |
| 35°   | 65.8  |
| 37.5° | 46.6  |
| 40°   | 32.7  |
| 42.5° | 22.7  |
| 45°   | 15.5  |
| 47.5° | 10.4  |
| 50°   | 6.8   |
| 52.5° | 5.2   |
| 55°   | 4.8   |
| 57.5° | 4.4   |
| 60°   | 4.0   |
| 62.5° | 3.6   |
| 65°   | 2.8   |
| 67.5° | 2.4   |
| 70°   | 2.4   |
| 72.5° | 2.0   |
| 75°   | 1.6   |
| 77.5° | 1.2   |
| 80°   | 1.2   |
| 82.5° | 0.8   |
| 85°   | 0.4   |
| 87.5° | 0.4   |



TEST NUMBER: P1289341

CATALOG NUMBER: P3AS05R35W2N902765DE010 E3DLP1WH\_5000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)